






Model	R_θ (°C/W)
ML9- - - - -	13.2




6296/6300 Series, ML 97 Series





Model	Dim. A mm (inches)	Dim. B mm (inches)	Dim. C mm (inches)	R _θ (°C/W)	Notes
6296B	-- 25.40 (1.000)	-- 21.59 (.850)	-- 3.81 (.150)	-- 4.7	▲
6298B	-- 38.10 (1.500)	-- 21.59 (.850)	-- 3.81 (.150)	-- 3.9	▲
ML97/1	-- 38.10 (1.500)	-- 21.59 (.850)	-- 3.60 (.142)	-- 3.9	
6299B	-- 50.80 (2.000)	-- 21.59 (.850)	-- 3.81 (.150)	-- 3.6	▲
ML97/1.5	-- 50.80 (2.000)	-- 21.59 (.850)	-- 3.60 (.142)	-- 3.6	
6300B	-- 63.50 (2.500)	-- 21.59 (.850)	-- 3.81 (.150)	-- 3.1	▲
ML97/2	-- 63.50 (2.500)	-- 21.59 (.850)	-- 3.60 (.142)	-- 3.1	

Model	Dim. A mm (inches)	Dim. B mm (inches)	Dim. C mm (inches)	R ₀ (°C/W)
6298B-2*	-- 38.10 (1.500)	-- 18.29 (.720)	--- 3.81 (.150)	--- 3.9
6299B-2*	-- 50.80 (2.000)	-- 18.29 (.720)	--- 3.81 (.150)	--- 3.6
6300B-2*	-- 63.50 (2.500)	-- 18.29 (.720)	--- 3.81 (.150)	--- 3.1

* Available, but not normally stocked.



▲ 6298B



Notes: To order optional solderable roll pin with shoulder for the 6296 Series, add "P2" after model number, e.g. 6298B-P2. Shoulder is $1.27 \pm .38 / .13 (.050 \pm .015 / .005)$ thick.
These parts are also available without roll pins: 6292B is 38.10mm (1.5") tall without roll pins, 6293B is 50.80mm (2.0") tall without roll pins, and 6294B is 63.50mm (2.5") tall without roll pins. Tolerances are $\pm .25 (.010)$ unless otherwise specified.

The Productivity Enhancements shown in the circles above are for use with the 6296 Series only.

1 6.35 (.250) x 10.92 (.430) notch on these parts only

2 Solderable roll pin (P1) standard as shown.

ML33

Model	R_{θ} ($^{\circ}\text{C/W}$)
ML33 - - - - -	8.5

