










Recommended Double-D Panel Cutout



Recommended Round Panel Cutout



Notes:

- Material and Finish:
 - Receptacle Housing & Protective Cover: Die-Cast, Nickel Plated
 - Panel Gasket: NBR, Color: Black
 - M3 Mounting Hardware: Stainless Steel includes 4 x (screw + nut + flat washer + spring lock washer)
 - Cover Gasket: Silicon, Color: White
 - Ball Chain Assembly, Copper Alloy and Stainless steel, Nickel Plated
- Duplex LC Adaptor Assembly:
 - Housing: Mod. PPO, UL94 V-0, Color: **SM Blue/MM Beige/APC SM Green**
 - Alignment Sleeves: SM Ceramic/MM Phosphor Bronze
 - Dust Cap: PP, Color: Neutral transparent
 - Operating Temperature: -40°C to +85°C
- Connector can be front or rear mounted to a maximum panel thickness of 3.2mm.
- IP67 rated when covered or fully mated with the appropriate mating connector
- Hardware shipped unassembled

Directive 2002/95/EC RoHS Compliant

Description	Part Number
Nickel Plated Die-Cast Duplex LC Single Mode Receptacle + Cover Assembly	17-300700
Nickel Plated Die-Cast Duplex LC Multi Mode Receptacle Cover Assembly	17-300710
Nickel Plated Die-cast Duplex LC APC Single Mode Receptacle Cover Assembly	17-300720

Customer:			Tolerance Unless otherwise specified		Autodesk Inventor	Scale:	Dim. in mm
Name	Title	Approval Date	0	PLC ±0.30			
			1	PLC ±0.20	2012	Date	Name
			2	PLC ±0.10			
			3	PLC ±0.05	Draw.	Apr. 17	Vincent Ke
				ANGLES ±1°			
					Appd.	Apr. 17	J. Chaudry
					Norm		
					D-old		
a	original				CONEC®		
Rev.	Changes	Date	Name				
Title: IP67 Industrial Duplex LC Receptacle (with Flange) + Cover Kit Nickel Plated Zinc Die-Cast Version						DIN A3	Sheet 1/1
Drawing No.: 17K1A327						Part No.: SEE PART NUMBER TABLE	