




7130






Model Material R_{θ} ($^{\circ}\text{C}/\text{W}$)
7130D --- Cu ----- 23.1




TV59, TV21, ML11



| Model | Device | DIM A mm (inches) | DIM B mm (inches) | DIM C mm (inches) | DIM D mm (inches) | DIM E mm (inches) | R_{θ} ($^{\circ}\text{C}/\text{W}$) mm (inches) |
|-------|-----------|----------------------|----------------------|----------------------|----------------------|----------------------|---|
| TV59 | Pentawatt | - | - | - | - | - | 9.9 |
| TV21 | -- TO-220 | 28.00 (1.102) | 14.70 (.579) | 3.20 (.126) | 3.70 (.146) | 5.10 (.201) | 9.9 |
| ML11 | -- TO-220 | 27.50 (1.083) | 12.20 (.480) | 8.30 (.327) | 3.60 (.142) | 10.00 (.394) | 9.9 |



▲ TV59



▲ TV21, ML11

TV40



Model R_{θ} ($^{\circ}\text{C}/\text{W}$)
TV40 ----- 9.9

