BGA Heat Sink (High Aspect Ratio Ext.) Custom Pin Fin





ATS Part#: ATS010010010-PF-1I

Description: 10.00 x 10.00 mm BGA Heat Sink (High Aspect Ratio Ext.) Custom Pin Fin

Heat Sink Type: Custom Pin Fin

Heat Sink Attachment: N/A
Equivalent Part Number: N/A

*Image above is for illustration purpose only.

Features & Benefits

- · High efficiency pin fin design provides low pressure drop characteristics
- · Large surface area increases heat sink performance
- · Fabricated from extruded aluminum, which minimizes thermal resistance from the base to the fins, reduces weight and keeps costs low
- · Comes standard without interface material or with most common pressure sensitive thermal tapes as a custom option

Thermal Performance

AIR VELOCITY		@200 LFM 1.0 M/S	@300 LFM 1.5 M/S	@400 LFM 2.0 M/S	@500 LFM 2.5 M/S	@600 LFM 3.0 M/S	@700 LFM 3.5 M/S	@800 LFM 4.0 M/S
THERMAL RESISTANCE	Unducted Flow	33.88 °C/W	28.2 °C/W	24.8 °C/W	22.4 °C/W	20.6 °C/W	19.2 °C/W	18.1 °C/W
	Ducted Flow	24.3	20.4	18.1	16.4	15.1	14.2	13.4

Product Detail





