



Safety Data Sheet

Copyright, 2015, 3M Company.

All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

Document Group:	34-6374-2	Version Number:	1.00
Issue Date:	07/14/15	Supersedes Date:	Initial Issue

SECTION 1: Identification

1.1. Product identifier

3M™ Novec™ Electronic Degreaser

Product Identification Numbers

98-0212-4889-7, 98-0212-4890-5

1.2. Recommended use and restrictions on use

Recommended use

Electronic Degreaser. For electronics use only. Not intended for use as a Medical Device or Drug.

Restrictions on use

Novec™ Aerosols are used in a wide variety of applications, including but not limited to precision cleaning of medical devices and as lubricant deposition solvents for medical devices. When the product is used for applications where the finished device is implanted into the human body, no residual Novec solvent may remain on the parts. It is highly recommended that the supporting test results and protocol be cited during FDA registration.

3M Electronics Markets Materials Division (EMMD) will not knowingly sample, support, or sell its products for incorporation in medical and pharmaceutical products and applications in which the 3M product will be temporarily or permanently implanted into humans or animals. The customer is responsible for evaluating and determining that a 3M EMMD product is suitable and appropriate for its particular use and intended application. The conditions of evaluation, selection, and use of a 3M product can vary widely and affect the use and intended application of a 3M product. Because many of these conditions are uniquely within the user's knowledge and control, it is essential that the user evaluate and determine whether the 3M product is suitable and appropriate for a particular use and intended application, and complies with all local applicable laws, regulations, standards, and guidance.

1.3. Supplier's details

MANUFACTURER:	3M
DIVISION:	Electronics Materials Solutions Division
ADDRESS:	3M Center, St. Paul, MN 55144-1000, USA
Telephone:	1-888-3M HELPS (1-888-364-3577)

1.4. Emergency telephone number

1-800-364-3577 or (651) 737-6501 (24 hours)

SECTION 2: Hazard identification

2.1. Hazard classification

Serious Eye Damage/Irritation: Category 2B.

Specific Target Organ Toxicity (central nervous system): Category 3.

2.2. Label elements**Signal word**

Warning

Symbols

Exclamation mark |

Pictograms**Hazard Statements**

Causes eye irritation.

May cause drowsiness or dizziness.

Precautionary Statements**Prevention:**

Avoid breathing dust/fume/gas/mist/vapors/spray.

Use only outdoors or in a well-ventilated area.

Wash thoroughly after handling.

Response:

IF INHALED: Remove person to fresh air and keep comfortable for breathing.

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

If eye irritation persists: Get medical advice/attention.

Call a POISON CENTER or doctor/physician if you feel unwell.

Storage:

Store in a well-ventilated place. Keep container tightly closed.

Store locked up.

Disposal:

Dispose of contents/container in accordance with applicable local/regional/national/international regulations.

2.3. Hazards not otherwise classified

None.

SECTION 3: Composition/information on ingredients

Ingredient	C.A.S. No.	% by Wt
1,2-Trans-dichloroethylene	156-60-5	65 - 75
Methyl nonafluoroisobutyl ether	163702-08-7	10 - 20
Methyl nonafluorobutyl ether	163702-07-6	5 - 15
Carbon dioxide	124-38-9	< 5

SECTION 4: First aid measures**4.1. Description of first aid measures**

Inhalation:

Remove person to fresh air. If you feel unwell, get medical attention.

Skin Contact:

Wash with soap and water. If you feel unwell, get medical attention.

Eye Contact:

Flush with large amounts of water. Remove contact lenses if easy to do. Continue rinsing. If signs/symptoms persist, get medical attention.

If Swallowed:

Rinse mouth. If you feel unwell, get medical attention.

4.2. Most important symptoms and effects, both acute and delayed

See Section 11.1. Information on toxicological effects.

4.3. Indication of any immediate medical attention and special treatment required

Not applicable.

SECTION 5: Fire-fighting measures**5.1. Suitable extinguishing media**

In case of fire: Use a fire fighting agent suitable for ordinary combustible material such as water or foam to extinguish.

5.2. Special hazards arising from the substance or mixture

None inherent in this product.

5.3. Special protective actions for fire-fighters

No special protective actions for fire-fighters are anticipated.

SECTION 6: Accidental release measures**6.1. Personal precautions, protective equipment and emergency procedures**

Evacuate area. Ventilate the area with fresh air. Refer to other sections of this SDS for information regarding physical and health hazards, respiratory protection, ventilation, and personal protective equipment.

6.2. Environmental precautions

Avoid release to the environment.

6.3. Methods and material for containment and cleaning up

Collect as much of the spilled material as possible. Place in a closed container approved for transportation by appropriate authorities. Dispose of collected material as soon as possible.

SECTION 7: Handling and storage**7.1. Precautions for safe handling**

Avoid breathing dust/fume/gas/mist/vapors/spray. Do not get in eyes, on skin, or on clothing. Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Avoid release to the environment.

7.2. Conditions for safe storage including any incompatibilities

Store in a well-ventilated place. Keep container tightly closed.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational exposure limits

If a component is disclosed in section 3 but does not appear in the table below, an occupational exposure limit is not available for the component.

Ingredient	C.A.S. No.	Agency	Limit type	Additional Comments
Carbon dioxide	124-38-9	ACGIH	TWA:5000 ppm;STEL:30000 ppm	
Carbon dioxide	124-38-9	OSHA	TWA:9000 mg/m3(5000 ppm)	
1,2-Trans-dichloroethylene	156-60-5	ACGIH	TWA:200 ppm	
Ethene, 1,2-dichloro-	156-60-5	OSHA	TWA:790 mg/m3(200 ppm)	
Methyl nonafluorobutyl ether	163702-07-6	AIHA	TWA:750 ppm	
Methyl nonafluoroisobutyl ether	163702-08-7	AIHA	TWA:750 ppm	

ACGIH : American Conference of Governmental Industrial Hygienists

AIHA : American Industrial Hygiene Association

CMRG : Chemical Manufacturer's Recommended Guidelines

OSHA : United States Department of Labor - Occupational Safety and Health Administration

TWA: Time-Weighted-Average

STEL: Short Term Exposure Limit

CEIL: Ceiling

8.2. Exposure controls

8.2.1. Engineering controls

Use general dilution ventilation and/or local exhaust ventilation to control airborne exposures to below relevant Exposure Limits and/or control dust/fume/gas/mist/vapors/spray. If ventilation is not adequate, use respiratory protection equipment.

8.2.2. Personal protective equipment (PPE)

Eye/face protection

Select and use eye/face protection to prevent contact based on the results of an exposure assessment. The following eye/face protection(s) are recommended:

Indirect Vented Goggles

Skin/hand protection

Select and use gloves and/or protective clothing approved to relevant local standards to prevent skin contact based on the results of an exposure assessment. Selection should be based on use factors such as exposure levels, concentration of the substance or mixture, frequency and duration, physical challenges such as temperature extremes, and other use conditions. Consult with your glove and/or protective clothing manufacturer for selection of appropriate compatible gloves/protective clothing.

Gloves made from the following material(s) are recommended: Nitrile Rubber

Respiratory protection

An exposure assessment may be needed to decide if a respirator is required. If a respirator is needed, use respirators as part of a full respiratory protection program. Based on the results of the exposure assessment, select from the following respirator type(s) to reduce inhalation exposure:

Half facepiece or full facepiece air-purifying respirator suitable for organic vapors

For questions about suitability for a specific application, consult with your respirator manufacturer.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

General Physical Form:	Liquid
Specific Physical Form:	Aerosol
Odor, Color, Grade:	Clear colorless liquid with slight odor. Contents under pressure.
Odor threshold	<i>No Data Available</i>
pH	<i>Not Applicable</i>
Melting point	<i>Not Applicable</i>
Boiling Point	43 °C
Flash Point	No flash point
Evaporation rate	<i>No Data Available</i>
Evaporation rate	<i>No Data Available</i>
Flammability (solid, gas)	Not Applicable
Flammable Limits(LEL)	6.7 % volume
Flammable Limits(UEL)	13.7 % volume
Vapor Pressure	330 mmHg
Vapor Density	<i>No Data Available</i>
Density	1.28 g/ml
Specific Gravity	1.28
Solubility in Water	Negligible
Solubility- non-water	<i>No Data Available</i>
Partition coefficient: n-octanol/ water	<i>No Data Available</i>
Autoignition temperature	396 °C
Decomposition temperature	<i>No Data Available</i>
Viscosity	0.45 centipoise

SECTION 10: Stability and reactivity**10.1. Reactivity**

This material may be reactive with certain agents under certain conditions - see the remaining headings in this section.

10.2. Chemical stability

Stable.

10.3. Possibility of hazardous reactions

Hazardous polymerization will not occur.

10.4. Conditions to avoid

Heat

10.5. Incompatible materials

Strong oxidizing agents

Strong bases

10.6. Hazardous decomposition products

<u>Substance</u>	<u>Condition</u>
Hydrogen Chloride	At Elevated Temperatures - - extreme conditions of heat
Hydrogen Fluoride	At Elevated Temperatures - - extreme conditions of heat
Perfluoroisobutylene (PFIB)	At Elevated Temperatures - - extreme conditions of heat

SECTION 11: Toxicological information

The information below may not be consistent with the material classification in Section 2 if specific ingredient classifications are mandated by a competent authority. In addition, toxicological data on ingredients may not be reflected in the material classification and/or the signs and symptoms of exposure, because an ingredient may be present below the threshold for labeling, an ingredient may not be available for exposure, or the data may not be relevant to the material as a whole.

11.1. Information on Toxicological effects

Signs and Symptoms of Exposure

Based on test data and/or information on the components, this material may produce the following health effects:

Inhalation:

Respiratory Tract Irritation: Signs/symptoms may include cough, sneezing, nasal discharge, headache, hoarseness, and nose and throat pain.

Skin Contact:

Contact with the skin during product use is not expected to result in significant irritation.

Eye Contact:

Moderate Eye Irritation: Signs/symptoms may include redness, swelling, pain, tearing, and blurred or hazy vision.

Ingestion:

Gastrointestinal Irritation: Signs/symptoms may include abdominal pain, stomach upset, nausea, vomiting and diarrhea.

May cause additional health effects (see below).

Additional Health Effects:

Single exposure may cause target organ effects:

Central Nervous System (CNS) Depression: Signs/symptoms may include headache, dizziness, drowsiness, incoordination, nausea, slowed reaction time, slurred speech, giddiness, and unconsciousness.

Toxicological Data

If a component is disclosed in section 3 but does not appear in a table below, either no data are available for that endpoint or the data are not sufficient for classification.

Acute Toxicity

Name	Route	Species	Value
Overall product	Ingestion		No data available; calculated ATE > 5,000 mg/kg
1,2-Trans-dichloroethylene	Dermal	Rabbit	LD50 > 5,000 mg/kg
1,2-Trans-dichloroethylene	Inhalation-Vapor (4 hours)	Rat	LC50 95.6 mg/l
1,2-Trans-dichloroethylene	Ingestion	Rat	LD50 7,902 mg/kg
Methyl nonafluoroisobutyl ether	Inhalation-Vapor (4 hours)	Rat	LC50 > 1,000 mg/l
Methyl nonafluoroisobutyl ether	Ingestion	Rat	LD50 > 5,000 mg/kg
Methyl nonafluorobutyl ether	Inhalation-Vapor (4 hours)	Rat	LC50 > 1,000 mg/l
Methyl nonafluorobutyl ether	Ingestion	Rat	LD50 > 5,000 mg/kg
Carbon dioxide	Inhalation-Gas (4 hours)	Rat	LC50 > 53,000 ppm

ATE = acute toxicity estimate

Skin Corrosion/Irritation

Name	Species	Value
1,2-Trans-dichloroethylene	Rabbit	Minimal irritation
Methyl nonafluoroisobutyl ether	Rabbit	No significant irritation
Methyl nonafluorobutyl ether	Rabbit	No significant irritation

Serious Eye Damage/Irritation

Name	Species	Value
1,2-Trans-dichloroethylene	Rabbit	Moderate irritant
Methyl nonafluoroisobutyl ether	Rabbit	No significant irritation
Methyl nonafluorobutyl ether	Rabbit	No significant irritation

Skin Sensitization

Name	Species	Value
Methyl nonafluoroisobutyl ether	Guinea pig	Not sensitizing
Methyl nonafluorobutyl ether	Guinea pig	Not sensitizing

Respiratory Sensitization

For the component/components, either no data are currently available or the data are not sufficient for classification.

Germ Cell Mutagenicity

Name	Route	Value
1,2-Trans-dichloroethylene	In Vitro	Not mutagenic
1,2-Trans-dichloroethylene	In vivo	Not mutagenic
Methyl nonafluoroisobutyl ether	In Vitro	Not mutagenic
Methyl nonafluoroisobutyl ether	In vivo	Not mutagenic
Methyl nonafluorobutyl ether	In Vitro	Not mutagenic
Methyl nonafluorobutyl ether	In vivo	Not mutagenic

Carcinogenicity

For the component/components, either no data are currently available or the data are not sufficient for classification.

Reproductive Toxicity**Reproductive and/or Developmental Effects**

Name	Route	Value	Species	Test Result	Exposure Duration
1,2-Trans-dichloroethylene	Inhalation	Some positive developmental data exist, but the data are not sufficient for classification	Rat	NOAEL 24 mg/l	during organogenesis
Methyl nonafluoroisobutyl ether	Inhalation	Not toxic to female reproduction	Rat	NOAEL 129 mg/l	1 generation
Methyl nonafluoroisobutyl ether	Inhalation	Not toxic to male reproduction	Rat	NOAEL 129 mg/l	1 generation
Methyl nonafluoroisobutyl ether	Inhalation	Some positive developmental data exist, but the data are not sufficient for classification	Rat	NOAEL 307 mg/l	during gestation
Methyl nonafluorobutyl ether	Inhalation	Not toxic to female reproduction	Rat	NOAEL 129 mg/l	1 generation
Methyl nonafluorobutyl ether	Inhalation	Not toxic to male reproduction	Rat	NOAEL 129 mg/l	1 generation
Methyl nonafluorobutyl ether	Inhalation	Some positive developmental data exist, but the data are not sufficient for classification	Rat	NOAEL 307 mg/l	during gestation
Carbon dioxide	Inhalation	Some positive male reproductive data exist, but the data are not sufficient for classification	Mouse	LOAEL 350,000 ppm	not available

Carbon dioxide	Inhalation	Some positive developmental data exist, but the data are not sufficient for classification	Rat	LOAEL 60,000 ppm	24 hours
----------------	------------	--	-----	------------------	----------

Target Organ(s)

Specific Target Organ Toxicity - single exposure

Name	Route	Target Organ(s)	Value	Species	Test Result	Exposure Duration
1,2-Trans-dichloroethylene	Inhalation	central nervous system depression	Some positive data exist, but the data are not sufficient for classification	Human	NOAEL Not available	occupational exposure
1,2-Trans-dichloroethylene	Inhalation	respiratory irritation	Some positive data exist, but the data are not sufficient for classification		NOAEL Not available	
1,2-Trans-dichloroethylene	Ingestion	central nervous system depression	May cause drowsiness or dizziness	Rat	LOAEL 4,500 mg/kg	not applicable
Methyl nonafluoroisobutyl ether	Inhalation	nervous system	Some positive data exist, but the data are not sufficient for classification	Dog	LOAEL 913 mg/l	10 minutes
Methyl nonafluoroisobutyl ether	Inhalation	cardiac sensitization	All data are negative	Dog	NOAEL 913 mg/l	10 minutes
Methyl nonafluorobutyl ether	Inhalation	nervous system	Some positive data exist, but the data are not sufficient for classification	Dog	LOAEL 913 mg/l	10 minutes
Methyl nonafluorobutyl ether	Inhalation	cardiac sensitization	All data are negative	Dog	NOAEL 913 mg/l	10 minutes

Specific Target Organ Toxicity - repeated exposure

Name	Route	Target Organ(s)	Value	Species	Test Result	Exposure Duration
1,2-Trans-dichloroethylene	Inhalation	endocrine system liver kidney and/or bladder respiratory system	All data are negative	Rat	NOAEL 16 mg/l	90 days
1,2-Trans-dichloroethylene	Ingestion	kidney and/or bladder	Some positive data exist, but the data are not sufficient for classification	Rat	NOAEL 2,000 mg/kg/day	14 weeks
1,2-Trans-dichloroethylene	Ingestion	blood liver	Some positive data exist, but the data are not sufficient for classification	Rat	NOAEL 125 mg/kg/day	14 weeks
1,2-Trans-dichloroethylene	Ingestion	heart immune system respiratory system	All data are negative	Rat	NOAEL 2,000 mg/kg/day	14 weeks
Methyl nonafluoroisobutyl ether	Inhalation	liver	Some positive data exist, but the data are not sufficient for classification	Rat	NOAEL 155 mg/l	13 weeks
Methyl nonafluoroisobutyl ether	Inhalation	bone, teeth, nails, and/or hair	Some positive data exist, but the data are not sufficient for classification	Rat	NOAEL 129 mg/l	11 weeks
Methyl nonafluoroisobutyl ether	Inhalation	heart skin endocrine system hematopoietic system immune system muscles nervous system eyes kidney and/or bladder respiratory system	All data are negative	Rat	NOAEL 155 mg/l	13 weeks
Methyl nonafluoroisobutyl ether	Ingestion	endocrine system liver	Some positive data exist, but the data are not sufficient for classification	Rat	NOAEL 1,000 mg/kg/day	28 days
Methyl nonafluoroisobutyl ether	Ingestion	heart hematopoietic system immune system nervous system eyes	All data are negative	Rat	NOAEL 1,000 mg/kg/day	28 days

		kidney and/or bladder respiratory system				
Methyl nonafluorobutyl ether	Inhalation	liver	Some positive data exist, but the data are not sufficient for classification	Rat	NOAEL 155 mg/l	13 weeks
Methyl nonafluorobutyl ether	Inhalation	bone, teeth, nails, and/or hair	Some positive data exist, but the data are not sufficient for classification	Rat	NOAEL 129 mg/l	11 weeks
Methyl nonafluorobutyl ether	Inhalation	heart skin endocrine system hematopoietic system immune system muscles nervous system eyes kidney and/or bladder respiratory system	All data are negative	Rat	NOAEL 155 mg/l	13 weeks
Methyl nonafluorobutyl ether	Ingestion	endocrine system liver	Some positive data exist, but the data are not sufficient for classification	Rat	NOAEL 1,000 mg/kg/day	28 days
Methyl nonafluorobutyl ether	Ingestion	heart hematopoietic system immune system nervous system eyes kidney and/or bladder respiratory system	All data are negative	Rat	NOAEL 1,000 mg/kg/day	28 days
Carbon dioxide	Inhalation	heart bone, teeth, nails, and/or hair liver nervous system kidney and/or bladder respiratory system	Some positive data exist, but the data are not sufficient for classification	Rat	LOAEL 60,000 ppm	166 days

Aspiration Hazard

For the component/components, either no data are currently available or the data are not sufficient for classification.

Please contact the address or phone number listed on the first page of the SDS for additional toxicological information on this material and/or its components.

SECTION 12: Ecological information**Ecotoxicological information**

Please contact the address or phone number listed on the first page of the SDS for additional ecotoxicological information on this material and/or its components.

Chemical fate information

Please contact the address or phone number listed on the first page of the SDS for additional chemical fate information on this material and/or its components.

SECTION 13: Disposal considerations**13.1. Disposal methods**

Dispose of contents/ container in accordance with the local/regional/national/international regulations.

Incinerate in a permitted waste incineration facility. Proper destruction may require the use of additional fuel during incineration processes. Combustion products will include halogen acid (HCl/HF/HBr). Facility must be capable of handling halogenated materials. As a disposal alternative, utilize an acceptable permitted waste disposal facility. Empty drums/barrels/containers used for transporting and handling hazardous chemicals (chemical substances/mixtures/preparations

classified as Hazardous as per applicable regulations) shall be considered, stored, treated & disposed of as hazardous wastes unless otherwise defined by applicable waste regulations. Consult with the respective regulating authorities to determine the available treatment and disposal facilities.

EPA Hazardous Waste Number (RCRA): Not regulated

SECTION 14: Transport Information

For Transport Information, please visit <http://3M.com/Transportinfo> or call 1-800-364-3577 or 651-737-6501.

SECTION 15: Regulatory information

15.1. US Federal Regulations

Contact 3M for more information.

311/312 Hazard Categories:

Fire Hazard - No Pressure Hazard - Yes Reactivity Hazard - No Immediate Hazard - Yes Delayed Hazard - No

Section 313 Toxic Chemicals subject to the reporting requirements of that section and 40 CFR part 372 (EPCRA):

<u>Ingredient</u>	<u>C.A.S. No</u>	<u>% by Wt</u>
1,2-Trans-dichloroethylene (Ethene, 1,2-dichloro-)	156-60-5	65 - 75

15.2. State Regulations

Contact 3M for more information.

15.3. Chemical Inventories

The components of this product are in compliance with the chemical notification requirements of TSCA.

Contact 3M for more information.

15.4. International Regulations

Contact 3M for more information.

This SDS has been prepared to meet the U.S. OSHA Hazard Communication Standard, 29 CFR 1910.1200.

SECTION 16: Other information

Document Group:	34-6374-2	Version Number:	1.00
Issue Date:	07/14/15	Supersedes Date:	Initial Issue

DISCLAIMER: The information in this Safety Data Sheet (SDS) is believed to be correct as of the date issued. 3M MAKES NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR COURSE OF PERFORMANCE OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of use or application. Given the variety of factors that can affect the use and application of a 3M product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for user's method of use or application.

3M provides information in electronic form as a service to its customers. Due to the remote possibility that electronic transfer

may have resulted in errors, omissions or alterations in this information, 3M makes no representations as to its completeness or accuracy. In addition, information obtained from a database may not be as current as the information in the SDS available directly from 3M

3M USA SDSs are available at www.3M.com