





NOTES:

- 適合ハウジング: 501189****
APPLICABLE 501330****
HOUSING 501939****
- めっき仕様: 表題欄参照
PLATING:SEE TABLE
- 本製品はコンタクト部 金めっき品である。
THIS PRODUCT IS GOLD PLATING FOR CONTACT POINT.
- 本製品はバレル外面 錫めっき品である。
THIS PRODUCT IS TIN PLATING OUTSIDE A BARREL.
- 圧着条件については、
圧着仕様書(CS-501193-001)を参照願います。
PLEASE REFER TO CRIMP SPECIFICATION (CS-501193-001).
- 製品の取扱いについては、コネクタ取扱い
説明書(5013300000 PS A00) を参照願います。
PLEASE REFER TO INSTRUCTION MANUAL(5013300000 PS A00).

1.27μm MIN.	0.9μm MIN.	0.76μm MIN.	5011935100	バラ状 LOOSE
			5011935000	連鎖状 CHAIN
		0.38μm MIN.	5011936100	バラ状 LOOSE
			5011936000	連鎖状 CHAIN
1.0μm MIN.		0.1μm MIN.	5011933100	バラ状 LOOSE
			5011933000	連鎖状 CHAIN
下地：ニッケルめっき UNDER PLATING: NICKEL PLATING	バレル外側：錫めっき OUTSIDE OF BARREL: TIN PLTAING	接点部：金めっき CONTACT AREA : GOLD PLATING	オーダー番号 ODER NO.	端子形状 FORM
めっき仕様(前めっき)：PLATING(PRE-PLATING)				

MATERIAL りん青銅 下地ニッケル、部分金めっき、錫めっき品 PHOSPHOR BRONZE t=0.12 SELECTIVE GOLD PLATING、SELECTIVE TIN PLATING、 UNDER NICKEL PLATING	
FINISH	SEE NOTE
WIRE RANGE	AWG#28-32
INS. RANGE	∅0.4-0.8

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																						
REDRAWN AND REVISED EC NO: 168346 DRWN: KYAMADA02 CHK'D: SAKIYAMA APPR: TKANEKO	2017/09/28 2017/11/30 2017/12/01	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		molex® PICO-CLASP 1.0 W/B CONN CRIMP REC TERM (GOLD PLATING)														
				mm		20:1																
		ANGULAR TOL ± 3.0 °		DRWN BY		DATE																
				QHE31		2017/04/03																
		4 PLACES ± 0.2		CHK'D BY		DATE																
				SAKIYAMA		2017/04/06																
	3 PLACES ± 0.2		APPR BY		DATE		PRODUCT CUSTOMER DRAWING															
	2 PLACES ± 0.2		TKANEKO		2017/04/06							SERIES 501193										
1 PLACE ± 0.2		DRAWING SIZE		THIRD ANGLE PROJECTION		MATERIAL NUMBER SEEB TABLE																
0 PLACES ± 0.2		A3		CUSTOMER																		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS											DOCUMENT NUMBER 5011930000											
B		REV							DOC TYPE PSD													
				DOC PART 000																		
														SHEET NUMBER 1 OF 1								