




TOLERANCE	
0-2.99 M	= +100.0/-25.0mm
3-8.99 M	= +150.0/-25.0mm
9-14.99 M	= +300.0/-25.0mm
15-OVER M	= +450.0/-25.0mm

REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
01	--	PRELIMINARY	06MAY19	SAM	TOMMY
02	--	UPDATE CABLE	16MAY19	SAM	TOMMY
03	--	CHANGE TE CONN P/N	12JUN19	SAM	TOMMY
04	--	CHANGE WIRING DIAGRAM	20JUN19	SAM	TOMMY
05	--	CHANGE PART NAME	21JAN21	SAM	TOMMY



WIRING DIAGRAM



NOTES: UNLESS OTHERWISE SPECIFIED

1 ALL PART DIMENSIONS ARE FOR REFERENCE ONLY.

2 CABLE ASSEMBLIES TO BE 100% TESTED FOR CONTINUITY, SHORTS, AND MIS-WIRES.

CUSTOMER DRAWING

QUANTITY	PART NUMBER	DESCRIPTION	ITEM
MATERIALS LIST			
UNLESS OTHERWISE SPECIFIED 1) All dimensions are in metric(mm). 2) Tolerances are as follows: 1 PL DEC ±0.30 2 PL DEC ±0.15 3 PL DEC ±0.08 3) Note reference =		SIGNATURES DRAWN: SAM CHECKED: SAM ENGINEER: APPROVAL: CUSTOMER:	DATE 21.JAN.21 21.JAN.21
MATERIAL SPECIFICATIONS: NOTED		THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.	
PROCESS SPECIFICATIONS: WHMA/IPC-A-620		SIZE A4 C-	REVISION 05
NEXT ASSY:		SCALE: NONE	DWG NO: P80896-Mxxx SHEET 1 OF 1

TITLE: CABLE ASSEMBLY,HARTING ASB4&ASB8  
DWG NO: P80896-Mxxx  
REV:05  
SH: 1  
OF: 1