

NOTES: UNLESS OTHERWISE SPECIFIED

1. TORQUE JAM NUT TO 110 IN-LBS USING 34mm SOCKET


2 METAL FEMALE DUST CAP MATERIAL WILL MATCH THE CONNECTOR MATERIAL OPTION AND ARE EMI COMPLIANT EXCEPT FOR (-3) BLACK ALUMINUM

3 MIXED WAVELENGTH CONNECTORS (850/1300 LENS ON THE RIGHT AND 1310/1550 ON THE LEFT AND DENOTED BY S&M MARKING ON THE INSERT) ARE AVAILABLE IN THE FOLLOWING CONFIGURATIONS:


- DM/2M - 2 CH STD, 850/1300, (M1,M2)
- TM/3M - 2 CH LEFT, 1310/1550, (S1, S2)
- QM/4M - 4 CH, 850/1300 RIGHT (M1, M2), 1310/1550 LEFT (S1, S2)

REVISION HISTORY - ALL SHEETS ARE THE SAME REVISION


REV	DESCRIPTION	DATE	APP
F	ECN 150504-1119, BDC	5/4/2015	BCull
G	ECN 181031-1814, RLF	2018/11/13	BCull
H	ECN 191204-1004, JC	2019/12/04	BCull
J	ECN 200302-1713, JC	2020/03/02	BCull




900µm (2, 3, 4)



2mm SIMPLEX (D, Q, T)



PANEL CUTOUT



EB4H8000 -

MATERIAL
8 - OD ALUMINUM
3 - BLACK ALUMINUM
Z - BLACK ZnNi ALUMINUM
A - MARINE BRONZE
B - 360 BRASS
C - 303 STAINLESS
F - 316 STAINLESS

CHANNELS
2 - 2 CH (STD), 900µm
3 - 2 CH (LEFT), 900µm
4 - 4 CH, 900µm
D - 2CH, 2mm SIMPLEX
Q - 4CH, 2mm SIMPLEX
T - 2CH, (LEFT) 2mm SIMPLEX

WAVELENGTH
1 - 850/1300 nm
2 - 1310 nm
3 - 1550 nm
4 - 1310/1550 nm
M - MIXED WAVELENGTH

DUST CAP
1 - OD NYLON HERMAPHRODITIC
2 - BROWN NYLON HERMAPHRODITIC
3 - BLACK NYLON HERMAPHRODITIC
4 - METAL FEMALE 2
(BLANK) - BLACK NYLON HERMAPHRODITIC


PRODUCT DRAWING

AmphenolFSI

DFT	XLT	02/04/2010
ENG	BCull	2010/02/04
CHK	BDC	2010/02/04
APP	JD	2010/02/04
DO NOT SCALE DRAWING UNLESS OTHERWISE SPECIFIED DIM ARE IN INCHES TOL ON ANGLES ±3 1 PL ±.1 2 PL ±.02 3 PL ±.010 INTERPRET DIM AND TOL PER ASME Y14.5-2009		
Copyright © 2018 Amphenol Fiber Systems International. Non published work. All rights reserved.		


TITLE			
RECEPTACLE ASSY, JAM NUT MOUNT			
SIZE	CAGE CODE	DWG NO	REV
C	ØYPM2	EB4H8000	J
SCALE 2:1		SHEET 1 OF 2	

2 CH (STD)
(OPTION 2)
OR
2 CH, 2mm SIMPLEX
(OPTION D)




WAVELENGTH OPTIONS 1-4

2 CH (LEFT)
(OPTION 3)
OR
2 CH (LEFT)
2mm SIMPLEX
(OPTION T)




WAVELENGTH OPTIONS 1-4


4 CH
(OPTION 4)
OR
4 CH, 2mm SIMPLEX
(OPTION Q)




WAVELENGTH OPTIONS 1-4



WAVELENGTH OPTION M
850/1300 (M1, M2)



WAVELENGTH OPTION M
1310/1550 (S1, S2)



WAVELENGTH OPTION M
850/1300 (M1, M2)
1310/1550 (S1, S2)

SIZE	CAGE CODE	DWG NO	REV
C	ØYPM2	EB4H8000	J
SCALE	2:1	SHEET	2 OF 2