



REV.	DATE	ECR NO.	DESCRIPTION
NC	06/28/00	XXXXXX	INITIAL RELEASE
A	01/20/14	2686	UPDATE DRAWING FORMAT



NOTE: ROCKWELL HARDNESS OF 65 MAX. ON 15-T SCALE
(HEAT TREAT FOR 45 MIN. AT 1100°F BEFORE PLATING)

NOTE: ROCKWELL HARDNESS OF 65 MAX. ON 15-T SCALE (HEAT TREAT FOR 45 MIN. AT 1100°F BEFORE PLATING)					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: <0.5 ± 0.05mm 0.5 - 6mm ± 0.10mm 6 - 30mm ± 0.20mm 30 - 120mm ± 0.30mm ANGLES ± 1° UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: <.020 ± 0.002" .020 - .236 = ± 0.004" .236 - 1.180 = ± 0.007" 1.180 - 4.724 = ± 0.012" ANGLES ± 1° DO NOT SCALE DRAWING		APPROVALS		DATE		Amphenol Connex						
							DRAWN		M.ZHANG							01/20/14	
							CHECKED						PART DESCRIPTION				
							ISSUED										
SHEET		1 OF 1				PART NO.											
CAD FILE		C:/CONNEX/FERRULE-223 .DWG				FERRULE-223											
1	FERRULE	BRASS	NICKEL	1	FERRULE-223												
	DESCRIPTION	MATERIAL	FINISH	QTY													
					DWG. NO. FERRULE-223 .DWG					REV. A		SIZE A		SCALE NA			