





REV	ECN	DESCRIPTION	APP'D
F	2687	REDRAW; THERMOSET TO PEI.	JR 5/13/96
G	3411	MRKG CORRECTION: PCD P/N	



NOTES:

- HOUSING - POLYETHERIMIDE, COLOR: BLUE-GREEN.
- SEALING GROMMET - SILICONE RUBBER PER ZZ-R-765, COLOR: RED.
- SOCKET CONTACT - COPPER ALLOY GOLD PLATED PER MIL-G-45204, TYPE II, GRADE C, CLASS I.
- STUD MATERIAL - STAINLESS STEEL, PASSIVATED.
- SOCKET CONTACTS ARE CLOSED ENTRY TYPE AND COMPLY WITH TEST REQUIREMENTS OF MIL-C-39029 INCLUDING CRIMP TERMINATION.
- M22520/1-01 CRIMP TOOL AND M22520/1-02 POSITIONER SHALL BE USED TO TERMINATE SOCKET CONTACTS TO THEIR RESPECTIVE WIRE SIZES.
- M81969/14-03 TOOL SHALL BE USED FOR INSERTING AND REMOVING WIRED SOCKET CONTACTS.
- ALL HARDWARE SUPPLIED UNASSEMBLED IN SEPERATE BAG WITHIN SOCKET PACKAGE.
- CONTACTS SUPPLIED IN SEPERATE RIGID CONTAINER WITHIN SOCKET PACKAGE.
- INSTALLATION TORQUE REQUIREMENTS:
THREAD SIZE 4-40 = 4 ±1.0 IN.-LBS.
THREAD SIZE 10-32 = 18 ±1.0 IN.-LBS.
- THE SEALING GROMMET IS DESIGNED TO SEAL OVER Ø.065-.109 WIRE.

PART NO.	CONTACTS SUPPLIED
RSL116072	NONE
RSL116073	20 SIZE-16/16 SOCKET CONTACT

DIMENSIONS	TOLERANCES	PROJECTION	REFERENCE SPECIFICATION	pcd	TITLE RELAY SOCKET (20) SIZE 16/16
ANSI Y14.5M UNITS: INCHES CRITICAL: ◆	.XX ± .01 .XXX ± .005 ANGLES ± 2°		M12883/47-10 DRWN A. PATRIE 5/6/96 ENGR J. RUTKOWSKI 5/13/96		
ORIGINAL NOT FOR CUSTOMER DISTRIBUTION	THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF PCD, INC. PEABODY, MA, USA		SIZE B	DWG NO. RSL116072	REV G
			CODE: 58982	SCALE: 1.5X	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[RSL116073-S](#) [RSL116072-S](#)