




2 x JACK SCREW



2 x PAN-HEAD SCREW



2 x COUNTERSUNK-HEAD SCREW



1 x CABLE STRAIN RELIEF

HOOD ASSEMBLY CONSISTS OF:

1. HOOD: ABS UL 94 V-0; METALLIZED
2. JACK SCREW: STEEL; NICKEL PLATED
3. COUNTERSUNK-HEAD SCREW: STEEL; NICKEL PLATED
4. PAN-HEAD SCREW: STEEL; NICKEL PLATED
5. CABLE STRAIN RELIEF: STEEL; NICKEL PLATED

TECHNICAL DATA:

TEMPERATURE RANGE: -35°C to + 90°C


Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

1 x b	Ä5307	25.08.2014	E.Mick.
a	Origin		
rev.	description	date	name

tolerance

2011	date	name
drawn	02.02.	Henneboel
appd.	02.02.	Fischer
norm		
d-old		



dim. in mm

scale:

1:1

material:

SEE NOTES

title:

PLASTIC HOOD
37pos.
with straight cable exit and jack screws

dwg no:

16K1A2775

DIN-A

4

sh: 1/1

part no:

165X13499A

CONEC®