


REV	ECN	DESCRIPTION	DATE	MODIFIED
1		PRE RELEASE	Sep-04-17	Rock
2		ADJUST DATAS	Sep-06-17	Rock
3		UPDATE DRAWING		



HVSLC632 06 2 0 4 I S 4

SERIES NUMBER

TYPE: PLUG




POS

KEY OPTION: A, B, C, D, E

INTERLOCK OPTION
1: YES
0: NO

WIRE SIZE: 4MM^2


SPECIAL: PLUG HVIL PASS THRU
SINGLE SHIELDED WIRE




TECHNICAL PARAMETERS
MATERIAL:
HOUSING: PA66 UL94-V0
CONTACT: COPPER ALLOY, TIN PLATED
SHIELDING: COPPER ALLOY, TIN PLATED
SEAL: SILICONE RUBBER


MACHENICAL DATAS:
DURABILITY: UP TO 100 CYCLES
IP67, IP2X
OPERATING TEMP. -40~125°C

ELECTRICAL DATAS
WITHSTAND VOLTAGE: 3000V AC
RATED CURRENT: 32A
RATED VOLTAGE: 1000V AC&DC
INSULATION RESISTANCE >200MΩ
CONTACT RESISTANCE: <2mΩ

DIMENSIONS	TOLERANCES	PROJECTION	Amphenol Pcd Shenzhen		TITLE				
ANSI Y14.5M	.X ±0.2		ENGR		HVSLC632 PLUG WITH PASS THRU HVIL				
UNITS: MM	.XX ±0.10		Rock Sep-04-17						
Pro/E FILE	ANGLES ±2.0°								
ORIGINAL	THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF AMPHENOL PCD SHENZHEN	CHKD		SIZE	DWG NO.		REV		
		APPD		A3	HVSLC632062A104IS4_C		3		
				CODE: 58982		SCALE:2:1		SHEET 1 OF 2	



SCALE 1:1



SCALE 2:1

12	C220011908	BACK COVER	1
11	C270011609	CABLE SEAL	1
10	C200011209	PLUG OUTER FERRULE	2
9	C200011210	PLUG INNER FERRULE	2
8	C31003623	POWER CONTACT,TIN FINISH	2
7	C31003613	SIGNAL CONTACT,TIN FINISH	2
6	C310023202	PLUG SHIELDLING,TIN FINISH	1
5	C220011806	PLUG INNER HOUSING,BLACK	1
4	C220011304	CPA,RED	1
3	C220011303X	PLUG BODY,ORANGE	1
2	C270011302	PLUG MATCH SEAL,RED	1
1	C220011305	PLUG SEAL BLOCK,BLACK	1
ITEMS	PART NUMBER	DESCRIPTION	QTY

SIZE	DWG NO.	REV
A3	HVSLC632062A104IS4_C	3
CODE: 58982	SCALE:	SHEET 2 OF 2