




SPECIFICATIONS

Current Rating: 3AMP
 Contact Resistance: 20mΩ Max
 Insulation Resistance: 1000MΩ Min
 Withstand Voltage: 1000V AC/minute
 Operation Temperature: -40 degree up +105 degree

Contact: Brass
 plating: Au or Sn Over 50u" Ni
 Insulator: High Temperature Thermoplastic
 UL94V-0 Rated
 Standard: PBT+30%G.F



Recommended PCB Layout

	T821	X	XX	XX	R1	00	C	EU	
Box Header: 2.54mm Pitch									
Housing Color 0: Grey 1: Black									
No of Positions: 06: 6 positions : : 64: 64 positions									
Plating Options: A1: Flash Gold A2: 15u"/0,4um Gold A3: 30u"/0,8um Gold SN: Tin									
									EU: RoHS Compliant
									C: Fixed Index
									Variation Code: 00: Standard
									Termination: S1: Straight THT R1: Right Angled THT



TOLERANCE (mm)	APPROVALS	DATE	TITLE	AMPHENOL
X. ±0.3	DRAWN Roger	12/Jun/2006	Box header, DIP	Amphenol European Design Center
X.X ±0.2	CHECKED Rob K.	13/Jun/2006	2.54mm, R/A	
X.XX ±0.15	APPROVED Rob K.	14/Jun/2006		
UNLESS OTHERWISE SPECIFIED	UNIT:	mm	SIZE: A4	Scale N.A. Sheet 1 of 1
			DRAWING N° T821X XX XX R100CEU	REV. A