






SECTION A-A



First pole



N=NUMBER OF POLES

DIM		Tolerance		
		1P--5P	6P--9P	10P--12P
Dim P	(N-1)×10.0	±0.40	±0.50	±0.60
Dim L	N×10.0±1.8	±0.40	±0.50	±0.60

PCB LAYOUT
TOP VIEW

SIGN	DATE	DESCRIPTION	APPROVER
△	11/12'12	change the product number	Da cheng
△	11/09'13	change the electrical specification /// update the drawing	Da cheng

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!

Material:

- Item ① Terminal body: Thermoplastic (UL94V-0)
- Item ② Terminal side body: Thermoplastic (UL94V-0)
- Item ③ Terminal cover: Thermoplastic (UL94V-0)
- Item ④ Spring clamp: Stainless steel
- Item ⑤ Solder pin: Copper, Tin Plated.

- Electrical: cULus
- Voltage rating: 300 V
- Current rating(SOL): 30 A
- Current rating(STR): 40 A
- Wire range:
- Solid wire(AWG): 8-20
- Stranded wire(AWG): 4-20
- Wire strip length: 18-19mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C ±5°C/5 Sec
- Safety Approval:
- Critical dimension:



NP xx 1 1 x 0 xxxx G

- No. OF POLES
- 01: 1POLES
- 02: 2 POLES
- 12: 12 POLES

- Body Color
- 0 Black (RAL9005)
- 2 Red (RAL3001/D)
- 3 Orange(RAL201/P)
- 4 Yellow(RAL1018/A)
- 5 Green(RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey(RAL7004/P)
- 9 White(RAL1102)
- C Multiple colors

RoHS compliant
(Lead<4%)
In copper Alloy

0000: "@" Logo (Standard)
000A: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	NP 10.0mm Series horizontal (A type 平行型)						
PART NO.	NPxx11x0xxxxG			DWG NO.	BNP0001		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Da cheng 2013.11.09	Da cheng 2013.11.09		UNIT: mm		X. ±0.50
					SCALE: NONE		X.X ±0.30
					REV: C		X.XX ±0.10
					SHEET: 01/01		X° ±1°