







SECTION P-P



RECOMMENDED PCB LAYOUT

N=Number of poles

Dim L	$(N-1) \times 3.50 + 4.9$
Dim B	$(N-1) \times 3.50$
Dim C	$(N-1) \times 3.50$

Poles	Dim B&Dim C	Dim L
2p	± 0.10	± 0.15
3p-6p	± 0.15	± 0.15
7p-12p	± 0.20	± 0.20
13p-16p	± 0.30	± 0.30

SIGN	DATE	DESCRIPTION	APPROVER
△			

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item ② Male contact pin: Copper Bright Tin plated over Nickel plated
- Item ⑥ Terminal(housing): LCP (UL94V-0)

Electrical:

- cULus
- Voltage rating: 300V
- Current rating: 10A
- Withstanding Voltage: 1.6KV
- Operating temperature: -45°C to $+130^{\circ}\text{C}$
- Reflow soldering temperature: $260^{\circ}\text{C}/10$ Sec Max.
- Safety Approval: cULus

OQ xx 1 G 0 1 xxxx G

No. OF POLES
02: 2 POLES
03: 3 POLES
:
16: 16 POLES

0 Black (RAL9005)

G RoHS compliant
(lead<4%)
In copper Alloy

0000: "@" Logo (Standard)

000A: "ANYTEK" Mark

Any special item by
customer request.
please contact sales
department.



Amphenol
ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	OQ 3.50mm 90° Series Close THR						
PART NO.	OQxx1G01xxxxG			DWG NO.	80Q0C17		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			
		CHENMING 10/22-16	CHENMING 10/22-16		SHEET: 01/01	UNIT: mm	X. ± 0.50
						SCALE: NONE	X.X ± 0.30
						REV.: B	X.XX ± 0.10
							X* $\pm 1^{\circ}$