








SIGN	DATE	DESCRIPTION	APPROVER
△			

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item ① Male contact pin: Copper, Bright Tin plated over Nickel plated
- Item ② Terminalhousing: LCP (UL94V-0)
- Item ③ With flange nut: STEEL, M2.5, Zinc plated

Electrical: cULus

- Voltage rating: 300V
- Current rating: 10A
- Withstanding Voltage: 1.6 KV
- Operating temperature: -45°C to +130°C
- Reflow soldering temperature: 260°C/10 Sec max
- Safety Approval: cULus

OQ xx 3 H x 1 xxxx G

No. OF POLES

- 02: 2 POLES
- 03: 3 POLES
- ...
- 16: 16 POLES

Color
0 Black (RAL9005)

G RoHS compliant
(lead<4%)
In copper Alloy

0000: "@" Logo (Standard)
000A: "ANYTEK" Mark
Any special item by
customer request,
please contact sales
department.

N=Number of poles

Dim L	(N-1)×3.81+14.2
Dim B	(N-1)×3.81
Dim D	(N-1)×3.81+9.0
Dim E	(N-1)×3.81
Dim F	(N-1)×3.81+9.0

Poles	Dim B & Dim E	Dim L & Dim D & Dim F
2p	±0.10	±0.15
3p-6p	±0.15	±0.15
7p-12p	±0.20	±0.20
13p-16p	±0.30	±0.30

Amphenol
ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR, PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		OQ 3.81mm 90° Series 2P-16P With flange THR				
PART NO.		OQxx3Hx1xxxxG		DWG NO.	80Q0E09	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance	
		CHENMING 2016.12.14	CHENMING 2016.12.14		UNIT: mm	X. ±0.50
					SCALE: NONE	X.X ±0.30
						X.XX ±0.10
					SHEET: 01/01	X° ±1°