

THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.



CUSTOMER DRAWING

REVISIONS					
REV#	ECR	REVISION ACTION	REV.BY:	APPR.BY:	DATE
A		INITIAL RELEASE	LQ	JL	06/09/2022


Amphenol TPI

2022-06-09


REGISTERED COPY



剖面 A-A
比例 5:1



剖面 B-B
比例 5:1



注(NOTES):

1. 对配公端直径 Mating contact diameter: 1.6mm
2. 额定电流 Current rating: 13A
3. 端子类型 Terminatin type: Crimp
4. 压线规格 Wire size: AWG16~18
5. 电镀信息 Plating specification:
镍底 镀锡
Tin over nickel
6. 材料规格 Material specification:
6.1. 端子: 铜合金 Contact body: Copper alloy
6.2. 外套: 不锈钢 Outer spring: Stainless steel
7. 符合ROHS ROHS complian

AMPHENOL
TPI

Amphenol Technical Products International Asia.

第三角投影 THIRD ANGLE PROJECTION	页面 SHEET	幅面 SIZE	版次 REV.	比例 SCALE	PART NAME:
1 OF 1	A4	A			HC Contact 16#Socket 16-18AWG
UNLESS OTHERWISE SPECIFIED: 1) All dimensions are in metric(mm). 2) Tolerances are as follows: 1.PL DEC ± 1.00 2.PL DEC ± 0.50 3.PL DEC ± 0.20 Angles ±1°					DWG NO: HCTF16164
					CUST PART # N/A
					CUST REV. A

Key
Characteristics
Contact
Amphenol for
Latest
Definition

签名 SIGNATURE

制图 DRAWN

LQ

审核 CHECKED

批准 APPROVAL

日期 DATE

06/09/2022



6/9/2022

THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.


CUSTOMER DRAWING

REVISIONS


REV#	ECR	REVISION ACTION	REV.BY:	APPR.BY:	DATE
A		INITIAL RELEASE	LQ	JL	06/09/2022



剖面 A-A
比例 5:1




剖面 B-B
比例 5:1



注(NOTES):

- 对配公端直径 Mating contact diameter:1.6mm
- 额定电流 Current rating: 13A
- 端子类型 Terminatin type: Crimp
- 压线规格 Wire size: AWG16~18
- 电镀信息 Plating specification:
镍底, 镀锡
Tin over nickel
- 材料规格 Material specification:
6.1. 端子: 铜合金 Contact body: Copper alloy
6.2. 外套: 不锈钢 Outer spring: Stainless steel
- 符合ROHS ROHS complian



Amphenol Technical Products International Asia.

第三角投影 THIRD ANGLE PROJECTION	页面 SHEET	幅面 SIZE	版次 REV.	比例 SCALE
	1 OF 1	A4	A	
UNLESS OTHERWISE SPECIFIED 1) All dimensions are in metric(mm). 2) Tolerances are as follows: 1.PL DEC ± 1.00 2.PL DEC ± 0.50 3.PL DEC ± 0.20 Angles ±1°				

PART NAME:	
HC Contact 16#Socket 16~18AWG	
DWG NO: HCTF16164	
CUST PART #	CUST REV.
N/A	A

Key Characteristics Critical Contact 关键特性	签名 SIGNATURE	日期 DATE
Amphenol for Latest Definition Significant 重点特性	制图 DRAWN	LQ
	审核 CHECKED	
	批准 APPROVAL	