




THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.

CUSTOMER DRAWING

REVISIONS					
REV#	ECR	REVISION ACTION	REV.BY:	APPR.BY:	DATE
A		INITIAL RELEASE	LQ	JL	06/09/2022



剖面 A-A
比例 5:1



剖面 B-B
比例 5:1



Amphenol TPI

2022 -06- 09

REGISTERED COPY

注(NOTES):

1. 对配母端直径 Mating contact diameter: 1.6mm
2. 额定电流 Current rating: 13A
3. 端子类型 Terminatin type: Crimp
4. 压线规格 Wire size: AWG16~18
5. 电镀信息 Plating specification:
镍底, 镀锡
Tin over nickel
6. 材料规格 Material specification:
6.1. 端子: 铜合金 Contact body: Copper alloy
6.2. 外套: 不锈钢 Outer spring: Stainless steel
7. 符合ROHS ROHS complian



Amphenol Technical Products International Asia.

第三角投影 THIRD ANGLE PROJECTION	页面 SHEET	幅面 SIZE	版次 REV.	比例 SCALE	PART NAME:
1 OF 1	A1	A	A		HC Contact 16#Pin 16-18AWG
UNLESS OTHERWISE SPECIFIED 1) All dimensions are in metric(mm). 2) Tolerances are as follows: 3. PL DEC ± 1.00 2. PL DEC ± 0.50 3. PL DEC ± 0.20					DWG NO: HCTM16164
CUST PART # N/A					CUST REV. A

Key Characteristics Contact Amphenol for Latest Definition	Critical 关键特性 Significant 重点特性
---	---

签名 SIGNATURE	日期 DATE
制图 DRAWN	LQ
审核 CHECKED	6/9/2022
批准 APPROVAL	



Angles ±1°

THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.


CUSTOMER DRAWING

REVISIONS


REV#	ECR	REVISION ACTION	REV.BY:	APPR.BY:	DATE
A		INITIAL RELEASE	LQ	JL	06/09/2022



剖面 A-A
比例 5:1




剖面 B-B
比例 5:1



注(NOTES):

- 对配母端直径 Mating contact diameter: 1.6mm
- 额定电流 Current rating: 13A
- 端子类型 Terminatin type: Crimp
- 压线规格 Wire size: AWG16~18
- 电镀信息 Plating specification:
镍底, 镀锡
Tin over nickel
- 材料规格 Material specification:
 - 端子: 铜合金 Contact body: Copper alloy
 - 外套: 不锈钢 Outer spring: Stainless steel
- 符合ROHS ROHS complian



Amphenol Technical Products International Asia.

第三角投影 THIRD ANGLE PROJECTION	页 面 SHEET	幅面 SIZE	版次 REV.	比例 SCALE	PART NAME: HC Contact 16#Pin 16-18AWG	
	1 OF 1	A4	A			
日期 DATE 06/09/2022	UNLESS OTHERWISE SPECIFIED 1) All dimensions are in metric(mm). 2) Tolerances are as follows: 1.PL DEC ± 1.00 2.PL DEC ± 0.50 3.PL DEC ± 0.20 Angles ±1°				DWG NO: HCTM16164	
					CUST PART # N/A	
					CUST REV. A	

Key Characteristics Critical
Contact 关键特性
Amphenol for Latest
Definition Significant
重点特性