



Amphenol



DIN Rail[®] Terminal Block

1.5mm²



APT-1.5/1-1



单层，一进一出接线端子
Single Layer, 1-1 Wiring Terminals

技术参数/Technical Parameter

APT-1.5/1-1 PE



单层，一进一出接地端子
Single Layer, 1-1 Grounding Terminal

技术参数/Technical Parameter


Part Number

APTS152SDxx00G

APTS152PEYG00G

Size(mm)

For 35x7.5(H)
For 35x15(H)



厚度/Thickness

宽度/Width

带U型导轨高度
With U-Shaped Guide Height

3.5

45

32

厚度/Thickness

宽度/Width

带U型导轨高度
With U-Shaped Guide Height

3.5

45

32

Rated Parameters

IEC60947-7-1

cULus

IEC60947-7-2

cULus

Rated Voltage(V)

500

300

/

/

Rated Current(A)

17.5

15

/

/

Wire Range

0.2-1.5mm²

AWG 26-14

0.2-1.5mm²

AWG 26-14

Strip Length(mm)

8-10

8-10

8-10

8-10

Safety Approval

CE

cULus

CE

cULus

附件/Attachments

附件/Attachments

End Plate

APT-1.5/1-1 SC


APT-1.5/1-1 SC

Part Number

APTS152SCxx00G

APTS152SCxx00G


APT-1.5/1-2



单层，一进两出接线端子
Single Layer, 1-2 Wiring Terminals

技术参数/Technical Parameter

APT-1.5/1-2 PE



单层，一进两出接地端子
Single Layer, 1-2 Grounding Terminal

技术参数/Technical Parameter


Part Number

APTS153SDxx00G

APTS153PEYG00G

Size(mm)

For 35x7.5(H)
For 35x15(H)



厚度/Thickness

宽度/Width

带U型导轨高度
With U-Shaped Guide Height

3.5

54.1

32

厚度/Thickness

宽度/Width

带U型导轨高度
With U-Shaped Guide Height

3.5

54.1

32

Rated Parameters

IEC60947-7-1

cULus

IEC60947-7-2

cULus

Rated Voltage(V)

500

300

/

/

Rated Current(A)

17.5

15

/

/

Wire Range

0.2-1.5mm²

AWG 26-14

0.2-1.5mm²

AWG 26-14

Strip Length(mm)

8-10

8-10

8-10

8-10

Safety Approval

CE

cULus

CE

cULus

附件/Attachments

附件/Attachments

End Plate

APT-1.5/1-2 SC



APT-1.5/1-2 SC

Part Number

APTS153SCxx00G

APTS153SCxx00G



APT-1.5/2-2



单层，两进两出接线端子
Single Layer, 2-2 Wiring Terminals

技术参数/Technical Parameter

APT-1.5/2-2 PE



单层，两进两出接地端子
Single Layer, 2-2 Grounding Terminal


技术参数/Technical Parameter

Part Number

APTS154SDxx00G

APTS154PEYG00G

Size(mm)



厚度/Thickness	宽度/Width	带U型导轨高度 With U-Shaped Guide Height
3.5	63.2	32

厚度/Thickness	宽度/Width	带U型导轨高度 With U-Shaped Guide Height
3.5	63.2	32

Rated Parameters

IEC60947-7-1	cULus
--------------	-------

IEC60947-7-2	cULus
--------------	-------

Rated Voltage(V)

500	300
-----	-----

/	/
---	---

Rated Current(A)

17.5	15
------	----

/	/
---	---

Wire Range

0.2-1.5mm ²	AWG 26-14
------------------------	-----------

0.2-1.5mm ²	AWG 26-14
------------------------	-----------

Strip Length(mm)

8-10	8-10
------	------

8-10	8-10
------	------

Safety Approval

CE	cULus
----	-------

CE	cULus
----	-------

附件/Attachments

附件/Attachments

End Plate

APT-1.5/2-2 SC



APT-1.5/2-2 SC

Part Number

APTS154SCxx00G

APTS154SCxx00G


APT-1.5/2*2



双层，两进两出接线端子
Double Layers, 2-2 Wiring Terminals

技术参数/Technical Parameter

APT-1.5/2*2 PE



双层，两进两出接地端子
Double Layers, 2-2 Grounding Terminal


技术参数/Technical Parameter

Part Number

APTD152SDxx00G

APTD152PEYG00G

Size(mm)



厚度/Thickness	宽度/Width	带U型导轨高度 With U-Shaped Guide Height
3.5	65.4	42.6

厚度/Thickness	宽度/Width	带U型导轨高度 With U-Shaped Guide Height
3.5	65.4	42.6

Rated Parameters

IEC60947-7-1	cULus
--------------	-------

IEC60947-7-2	cULus
--------------	-------

Rated Voltage(V)

500	300
-----	-----

/	/
---	---

Rated Current(A)

16	15
----	----

/	/
---	---

Wire Range

0.2-1.5mm ²	AWG 26-14
------------------------	-----------

0.2-1.5mm ²	AWG 26-14
------------------------	-----------

Strip Length(mm)

8-10	8-10
------	------

8-10	8-10
------	------

Safety Approval

CE	cULus
----	-------

CE	cULus
----	-------

附件/Attachments

附件/Attachments

End Plate

APT-1.5/2*2 SC

APT-1.5/2*2 SC



Part Number

APTD152SCxx00G

APTD152SCxx00G

2.5mm²


APT-2.5/1-1



单层，一进一出接线端子
Single Layer, 1-1 Wiring Terminals

技术参数/Technical Parameter

APT-2.5/1-1 PE



单层，一进一出接地端子
Single Layer, 1-1 Grounding Terminal

技术参数/Technical Parameter

Part Number

APTS252SDxx00G

APTS252PEYG00G

Size(mm)

For 35x7.5(H)
For 35x15(H)

厚度/Thickness

宽度/Width

带U型导轨高度
With U-Shaped Guide Height

5.2

48.6

36.8

厚度/Thickness

宽度/Width

带U型导轨高度
With U-Shaped Guide Height

5.2

48.6

36.8

Rated Parameters

IEC60947-7-1

cULus

IEC60947-7-2

cULus

Rated Voltage(V)

800

600

/

/

Rated Current(A)

24

20

/

/

Wire Range

0.2-4mm²

AWG 26-12

0.2-4mm²

AWG 26-12

Strip Length(mm)

8-10

8-10

8-10

8-10

Safety Approval

CE

cULus

CE

cULus

附件/Attachments

附件/Attachments

End Plate

APT-2.5/1-1 SC


APT-2.5/1-1 SC

Part Number

APTS252SCxx00G

APTS252SCxx00G


APT-2.5/1-2



单层，一进两出接线端子
Single Layer, 1-2 Wiring Terminals

技术参数/Technical Parameter

APT-2.5/1-2 PE



单层，一进两出接地端子
Single Layer, 1-2 Grounding Terminal

技术参数/Technical Parameter

Part Number

APTS253SDxx00G

APTS253PEYG00G

Size(mm)

For 35x7.5(H)
For 35x15(H)

厚度/Thickness

宽度/Width

带U型导轨高度
With U-Shaped Guide Height

5.2

60.4

36.8

厚度/Thickness

宽度/Width

带U型导轨高度
With U-Shaped Guide Height

5.2

60.4

36.8

Rated Parameters

IEC60947-7-1

cULus

IEC60947-7-2

cULus

Rated Voltage(V)

800

600

/

/

Rated Current(A)

24

20

/

/

Wire Range

0.2-4mm²

AWG 26-12

0.2-4mm²

AWG 26-12

Strip Length(mm)

8-10

8-10

8-10

8-10

Safety Approval

CE

cULus

CE

cULus

附件/Attachments

附件/Attachments

End Plate

APT-2.5/1-2 SC



APT-2.5/1-2 SC

Part Number

APTS253SCxx00G

APTS253SCxx00G


APT-2.5/2-2



单层，两进两出接线端子
Single Layer, 2-2 Wiring Terminals

技术参数/Technical Parameter

APT-2.5/2-2 PE



单层，两进两出接地端子
Single Layer, 2-2 Grounding Terminal


技术参数/Technical Parameter

Part Number

APTS254SDxx00G

APTS254PEYG00G

Size(mm)



厚度/Thickness

宽度/Width

带U型导轨高度
With U-Shaped Guide Height

5.2

72.4

36.8

Rated Parameters

IEC60947-7-1

cULus

Rated Voltage(V)

800

600

Rated Current(A)

24

20

Wire Range

0.2-4mm²

AWG 26-12

Strip Length(mm)

8-10

8-10

Safety Approval



附件/Attachments

End Plate

APT-2.5/2-2 SC

Part Number

APTS254SCxx00G

厚度/Thickness

宽度/Width

带U型导轨高度
With U-Shaped Guide Height

5.2

72.4

36.8

IEC60947-7-2

cULus

/

/

/

/

0.2-4mm²

AWG 26-12

8-10

8-10





附件/Attachments

APT-2.5/2-2 SC

APTS254SCxx00G


APT-2.5/2*2



双层，两进两出接线端子
Double Layers, 2-2 Wiring Terminals

技术参数/Technical Parameter

APT-2.5/2*2 PE



双层，两进两出接地端子
Double Layers, 2-2 Grounding Terminal


技术参数/Technical Parameter

Part Number

APTD252SDxx00G

APTD252PEYG00G

Size(mm)



厚度/Thickness

宽度/Width

带U型导轨高度
With U-Shaped Guide Height

5.2

68.4

47.6

Rated Parameters

IEC60947-7-1

cULus

Rated Voltage(V)

500

300

Rated Current(A)

22

20

Wire Range

0.2-4mm²

AWG 26-12

Strip Length(mm)

8-10

8-10

Safety Approval



附件/Attachments

End Plate

APT-2.5/2*2 SC

Part Number

APTD252SCxx00G

厚度/Thickness

宽度/Width

带U型导轨高度
With U-Shaped Guide Height

5.2

68.4

47.6

IEC60947-7-2

cULus

/

/

/

/

0.2-4mm²

AWG 26-12

8-10

8-10




附件/Attachments

APT-2.5/2*2 SC

APTD252SCxx00G

2.5mm²


APT-2.5/3*2



三层，三进三出接线端子
Three layers, 3-3 Wiring Terminals


技术参数/Technical Parameter

APT-2.5/3*2 PE




三层，三进三出接地端子
Three layers, 3-3 Grounding Terminal

技术参数/Technical Parameter

Part Number		APTT252SDxx00G			APTT252PEYG00G		
Size(mm)		厚度/Thickness	宽度/Width	带U型导轨高度 With U-Shaped Guide Height	厚度/Thickness	宽度/Width	带U型导轨高度 With U-Shaped Guide Height
		5.2	102.2	58	5.2	102.2	58
Rated Parameters		IEC60947-7-1		cULus	IEC60947-7-2		cULus
Rated Voltage(V)		500		300	/		/
Rated Current(A)		20		20	/		/
Wire Range		0.2-4mm ²		AWG 26-12	0.2-4mm ²		AWG 26-12
Strip Length(mm)		8-10		8-10	8-10		8-10
Safety Approval		CE		cULus	CE		cULus
		附件/Attachments			附件/Attachments		
End Plate		APT-2.5/3*2 SC			APT-2.5/3*2 SC		
Part Number		APTT252SCxx00G			APTT252SCxx00G		


APT-4/1-1



单层，一进一出接线端子
Single Layer, 1-1 Wiring Terminals

技术参数/Technical Parameter

APT-4/1-1 PE



单层，一进一出接地端子
Single Layer, 1-1 Grounding Terminal


技术参数/Technical Parameter

Part Number

APTS042SDxx00G

APTS042PEYG00G

Size(mm)



厚度/Thickness

6.2

宽度/Width

55.8

带U型导轨高度
With U-Shaped Guide Height

36.8

厚度/Thickness

6.2

宽度/Width

55.8

带U型导轨高度
With U-Shaped Guide Height

36.8

Rated Parameters

IEC60947-7-1

cULus

IEC60947-7-2

cULus

Rated Voltage(V)

800

600

/

/

Rated Current(A)

32

30

/

/

Wire Range

0.2-6mm²

AWG 24-10

0.2-6mm²

AWG 24-10

Strip Length(mm)

10-12

10-12

10-12

10-12

Safety Approval

CE

cULus

CE

cULus

附件/Attachments

附件/Attachments

End Plate

APT-4/1-1 SC


APT-4/1-1 SC

Part Number

APTS042SCxx00G

APTS042SCxx00G


APT-4/1-2



单层，一进两出接线端子
Single Layer, 1-2 Wiring Terminals

技术参数/Technical Parameter

APT-4/1-2 PE



单层，一进两出接地端子
Single Layer, 1-2 Grounding Terminal


技术参数/Technical Parameter

Part Number

APTS043SDxx00G

APTS043PEYG00G

Size(mm)



厚度/Thickness

6.2

宽度/Width

66.4

带U型导轨高度
With U-Shaped Guide Height

36.8

厚度/Thickness

6.2

宽度/Width

66.4

带U型导轨高度
With U-Shaped Guide Height

36.8

Rated Parameters

IEC60947-7-1

cULus

IEC60947-7-2

cULus

Rated Voltage(V)

800

600

/

/

Rated Current(A)

32

30

/

/

Wire Range

0.2-6mm²

AWG 24-10

0.2-6mm²

AWG 24-10

Strip Length(mm)

10-12

10-12

10-12

10-12

Safety Approval

CE

cULus

CE

cULus

附件/Attachments

附件/Attachments

End Plate

APT-4/1-2 SC

APT-4/1-2 SC


Part Number

APTS043SCxx00G

APTS043SCxx00G

4mm²


APT-4/2-2



单层，两进两出接线端子
Single Layer, 2-2 Wiring Terminals

技术参数/Technical Parameter

APT-4/2-2 PE



单层，两进两出接地端子
Single Layer, 2-2 Grounding Terminal

技术参数/Technical Parameter

Part Number

APTS044SDxx00G

APTS044PEYG00G

Size(mm)

For 35x7.5(H)
For 35x15(H)

厚度/Thickness

宽度/Width

带U型导轨高度
With U-Shaped Guide Height

6.2

76.9

36.8

厚度/Thickness

宽度/Width

带U型导轨高度
With U-Shaped Guide Height

6.2

76.9

36.8

Rated Parameters

IEC60947-7-1

cULus

IEC60947-7-2

cULus

Rated Voltage(V)

800

600

/

/

Rated Current(A)

32

30

/

/

Wire Range

0.2-6mm²

AWG 24-10

0.2-6mm²

AWG 24-10

Strip Length(mm)

10-12

10-12

10-12

10-12

Safety Approval

CE

cULus

CE

cULus

附件/Attachments

附件/Attachments

End Plate

APT-4/2-2 SC


APT-4/2-2 SC

Part Number

APTS044SCxx00G

APTS044SCxx00G


APT-4/2*2



双层，两进两出接线端子
Double Layers, 2-2 Wiring Terminals

技术参数/Technical Parameter

APT-4/2*2 PE



双层，两进两出接地端子
Double Layers, 2-2 Grounding Terminal

技术参数/Technical Parameter

Part Number

APTD042SDxx00G

APTD042PEYG00G

Size(mm)

For 35x7.5(H)
For 35x15(H)

厚度/Thickness

宽度/Width

带U型导轨高度
With U-Shaped Guide Height

6.2

83.7

47.4

厚度/Thickness

宽度/Width

带U型导轨高度
With U-Shaped Guide Height

6.2

83.7

47.4

Rated Parameters

IEC60947-7-1

cULus

IEC60947-7-2

cULus

Rated Voltage(V)

500

300

/

/

Rated Current(A)

28

28

/

/

Wire Range

0.2-6mm²

AWG 24-10

0.2-6mm²

AWG 24-10

Strip Length(mm)

10-12

10-12

10-12

10-12

Safety Approval

CE

cULus

CE

cULus

附件/Attachments

附件/Attachments

End Plate

APT-4/2*2 SC



APT-4/2*2 SC

Part Number

APTD042SCxx00G

APTD042SCxx00G


APT-6/1-1



单层，一进一出接线端子
Single Layer, 1-1 Wiring Terminals

技术参数/Technical Parameter

APT-6/1-1 PE



单层，一进一出接地端子
Single Layer, 1-1 Grounding Terminal


技术参数/Technical Parameter

Part Number

APTS062SDxx00G

APTS062PEYG00G

Size(mm)



厚度/Thickness

宽度/Width

带U型导轨高度
With U-Shaped Guide Height

8.2

57.7

43.7

Rated Parameters

IEC60947-7-1

cULus

Rated Voltage(V)

1000

600

Rated Current(A)

41

40

Wire Range

0.5-10mm²

Str. 20-8 AWG
Sol. 20-10 AWG

Strip Length(mm)

10-12

10-12

Safety Approval



附件/Attachments

End Plate

APT-6/1-1 SC

Part Number

APTS062SCxx00G

厚度/Thickness

宽度/Width

带U型导轨高度
With U-Shaped Guide Height

8.2

57.7

43.7

IEC60947-7-2

cULus

/

/

/

/

0.5-10mm²

Str. 20-8 AWG
Sol. 20-10 AWG

10-12

10-12




附件/Attachments

APT-6/1-1 SC

APTS062SCxx00G


APT-6/1-2



单层，一进两出接线端子
Single Layer, 1-2 Wiring Terminals

技术参数/Technical Parameter

APT-6/1-2 PE



单层，一进两出接地端子
Single Layer, 1-2 Grounding Terminal


技术参数/Technical Parameter

Part Number

APTS063SDxx00G

APTS063PEYG00G

Size(mm)



厚度/Thickness

宽度/Width

带U型导轨高度
With U-Shaped Guide Height

8.2

74.1

43.7

Rated Parameters

IEC60947-7-1

cULus

Rated Voltage(V)

1000

600

Rated Current(A)

41

40

Wire Range

0.5-10mm²

Str. 20-8 AWG
Sol. 20-10 AWG

Strip Length(mm)

10-12

10-12

Safety Approval



附件/Attachments

End Plate

APT-6/1-2 SC

Part Number

APTS063SCxx00G

厚度/Thickness

宽度/Width

带U型导轨高度
With U-Shaped Guide Height

8.2

74.1

43.7

IEC60947-7-2

cULus

/

/

/

/

0.5-10mm²

Str. 20-8 AWG
Sol. 20-10 AWG

10-12

10-12





附件/Attachments

APT-6/1-2 SC

APTS063SCxx00G

6mm²


APT-6/2-2



单层，两进两出接线端子
Single Layer, 2-2 Wiring Terminals


技术参数/Technical Parameter

APT-6/2-2 PE




单层，两进两出接地端子
Single Layer, 2-2 Grounding Terminal

技术参数/Technical Parameter

Part Number	APTS064SDxx00G			APTS064PEYG00G		
Size(mm)	厚度/Thickness	宽度/Width	带U型导轨高度 With U-Shaped Guide Height	厚度/Thickness	宽度/Width	带U型导轨高度 With U-Shaped Guide Height
For 35×7.5(H) For 35×15(H) 	8.2	90.5	43.7	8.2	90.5	43.7
Rated Parameters	IEC60947-7-1		cULus	IEC60947-7-2		cULus
Rated Voltage(V)	1000		600	/		/
Rated Current(A)	41		40	/		/
Wire Range	0.5-10mm ²		Str. 20-8 AWG Sol. 20-10 AWG	0.5-10mm ²		Str. 20-8 AWG Sol. 20-10 AWG
Strip Length(mm)	10-12		10-12	10-12		10-12
Safety Approval	CE		cULus	CE		cULus
	附件/Attachments			附件/Attachments		
End Plate	APT-6/2-2 SC			APT-6/2-2 SC		
Part Number	APTS064SCxx00G			APTS064SCxx00G		


APT-10/1-1



单层，一进一出接线端子
Single Layer, 1-1 Wiring Terminals

技术参数/Technical Parameter

APT-10/1-1 PE



单层，一进一出接地端子
Single Layer, 1-1 Grounding Terminal


技术参数/Technical Parameter

Part Number

APTS102SDxx00G

APTS102PEYG00G

Size(mm)



厚度/Thickness

10.2

宽度/Width

67.7

带U型导轨高度
With U-Shaped Guide Height

51.1

厚度/Thickness

10.2

宽度/Width

67.7

带U型导轨高度
With U-Shaped Guide Height

51.1

Rated Parameters

IEC60947-7-1

cULus

Rated Voltage(V)

1000

600

Rated Current(A)

57

60

Wire Range

0.5-16mm²

Str. 20-6 AWG
Sol. 20-10 AWG

Strip Length(mm)

18

18

Safety Approval



附件/Attachments

End Plate

APT-10/1-1 SC

Part Number

APTS102SCxx00G

IEC60947-7-2

cULus

/

/

/

/

0.5-16mm²

Str. 20-6 AWG
Sol. 20-10 AWG

18

18




附件/Attachments

APT-10/1-1 SC

APTS102SCxx00G


APT-10/1-2



单层，一进两出接线端子
Single Layer, 1-2 Wiring Terminals

技术参数/Technical Parameter

APT-10/1-2 PE



单层，一进两出接地端子
Single Layer, 1-2 Grounding Terminal


技术参数/Technical Parameter

Part Number

APTS103SDxx00G

APTS103PEYG00G

Size(mm)



厚度/Thickness

10.2

宽度/Width

88.9

带U型导轨高度
With U-Shaped Guide Height

51.1

厚度/Thickness

10.2

宽度/Width

88.9

带U型导轨高度
With U-Shaped Guide Height

51.1

Rated Parameters

IEC60947-7-1

cULus

Rated Voltage(V)

1000

600

Rated Current(A)

57

60

Wire Range

0.5-16mm²

Str. 20-6 AWG
Sol. 20-10 AWG

Strip Length(mm)

18

18

Safety Approval



附件/Attachments

End Plate

APT-10/1-2 SC

Part Number

APTS103SCxx00G

IEC60947-7-2

cULus

/

/

/

/

0.5-16mm²

Str. 20-6 AWG
Sol. 20-10 AWG

18

18




附件/Attachments

APT-10/1-2 SC

APTS103SCxx00G

16mm²


APT-16/1-1



单层，一进一出接线端子
Single Layer, 1-1 Wiring Terminals


技术参数/Technical Parameter

APT-16/1-1 PE




单层，一进一出接地端子
Single Layer, 1-1 Grounding Terminal

技术参数/Technical Parameter

Part Number	APTS162SDxx00G			APTS162PEYG00G		
Size(mm)	厚度/Thickness	宽度/Width	带U型导轨高度 With U-Shaped Guide Height	厚度/Thickness	宽度/Width	带U型导轨高度 With U-Shaped Guide Height
For 35x7.5(H) For 35x15(H) 	12.2	75.4	54.1	12.2	75.4	54.1
Rated Parameters	IEC60947-7-1		cULus	IEC60947-7-2		cULus
Rated Voltage(V)	1000		600	/		/
Rated Current(A)	76		85	/		/
Wire Range	0.5-25mm ²		Str. 20-4 AWG Sol. 20-10 AWG	0.5-25mm ²		Str. 20-4 AWG Sol. 20-10 AWG
Strip Length(mm)	18		18	18		18
Safety Approval	CE		cULus	CE		cULus
	附件/Attachments			附件/Attachments		
End Plate	APT-16/1-1 SC			APT-16/1-1 SC		
Part Number	APTS162SCxx00G			APTS162SCxx00G		



APT-16/1-2



单层，一进两出接线端子
Single Layer, 1-2 Wiring Terminals


技术参数/Technical Parameter

APT-16/1-2 PE



单层，一进两出接地端子
Single Layer, 1-2 Grounding Terminal

技术参数/Technical Parameter

Part Number	APTS163SDxx00G			APTS163PEYG00G		
Size(mm)	厚度/Thickness	宽度/Width	带U型导轨高度 With U-Shaped Guide Height	厚度/Thickness	宽度/Width	带U型导轨高度 With U-Shaped Guide Height
For 35x7.5(H) For 35x15(H) 	12.2	100.2	54.1	12.2	100.2	54.1
Rated Parameters	IEC60947-7-1		cULus	IEC60947-7-2		cULus
Rated Voltage(V)	1000		600	/		/
Rated Current(A)	76		85	/		/
Wire Range	0.5-25mm ²		Str. 20-4 AWG Sol. 20-10 AWG	0.5-25mm ²		Str. 20-4 AWG Sol. 20-10 AWG
Strip Length(mm)	18		18	18		18
Safety Approval	CE		cULus	CE		cULus
	附件/Attachments			附件/Attachments		
End Plate	APT-16/1-2 SC			APT-16/1-2 SC		
Part Number	APTS163SCxx00G			APTS163SCxx00G		

Application Field

- Power Grid
- Mechanical
- Transportation
- Communication
- Automation
- Construction



Nomenclature

APT		X	XX	X	XX	XX	X	X	X
		Number of layer	Wire cross section(mm ²)	Single Layer Number of Wire Inlet Holes	Category	Color			
S:	Single layer	15:	1.5 mm ²	2:	2 holes	GY:	Grey	00G	Standard
D:	Double layers	25:	2.5 mm ²	3:	3 holes	BK:	Black	XXG	Special
T:	Three layers	04:	4 mm ²	4:	4 holes	YG:	Yellow-Green		
		06:	6 mm ²			BU:	Blue		
		10:	10 mm ²			OG:	Orange		
		16:	16 mm ²						
					SD:				
					PE:	Standard			
					SC:	Grounding			
					FU:	Side Cover			
					EB:	Fuse			
						Upper and Lower With Equipotential Bonder			

ANYTEK®

Anytek Electronic Technology (SZ) Co., Ltd.
恩尼特克电子科技（深圳）有限公司

Web Site: <https://www.anytek.com.cn>
<http://www.anytek.com.tw>
E-mail: anytek@anytek.com.cn

Taiwan Taipei

新北市汐止区新台五路一段77号5楼之6
5F-6, No.77, Sec. 1, Xintai 5th Rd., Xizhi Dist.,
New Taipei City 22175, Taiwan, R.O.C.
Tel: +886-(0)2-26980366
Fax: +886-(0)2-26980377
E-mail: anytek@anytek.com.tw

China Shenzhen Factory

深圳市龙岗区坪地街道中心社区佳乐街10、13、13-1号，燕宝街1-3号
No. 10, 13, 13-1, Jiale Street and No. 1-3, Yanbao Street, Center Community,
Pingdi Street, Longgang District, Shenzhen City, China
工厂电话(Tel): +86-(0)755-84096008
工厂传真(Fax): +86-(0)755-84096027
销售电话(Tel): +86-(0)755-36518520/36518521
E-mail: anytek@anytek.com.cn

China Shanghai Office & Factory

上海市浦东新区金桥开发区宁桥路825号5号楼103室
Room 103, 5th Building, No. 825, Ning Qiao Road, Jinqiao
Development Zone, Pu Dong New District, Shanghai City, China
Tel: +86-(0)21-58999106
Fax: +86-(0)21-58993286
E-mail: anytek@anytek.com.cn

China Beijing Office

北京市海淀区上地十街1号院5号楼1509室
Room 1509, 5th Building, No. 1 Yard, Shangdi 10th Road,
Haidian District, Beijing City, China
Tel: +86-(0)10-62669285
Fax: +86-(0)10-59741667
E-mail: anytek@anytek.com.cn

Korea Branch Office & Factory

101, 1F, 728-6, Kumjung-Dong, Kunpo-City,
Kyounggi-Do, Korea
Tel: +82-(0)31-4557920
Fax: +82-(0)31-4548844
E-mail: dhkoh@anytekkorea.com

WARNING:

All the copyrights of this book belong to Anytek Technology Corporation Ltd., and it's prohibited for duplication. Once the duplication has been found, we will suit for law.

NOTE:

The information furnished by ANYTEK has been carefully checked and is believed to be assumed by ANYTEK. For its use, nor for an infringements of patents or other rights of third parties that may result from its use. ANYTEK retains the rights to make changes in the publication without prior notice.