






Amphenol PCDSZ
ORIGINAL
PDF Format
R&D

REV	ECN	DESCRIPTION	DATE	MODIFIED
B		UPDATE	2018.06.18	ROY.QU



TECHNICAL FEATURES

1. MATERIAL:
CONTACT: COPPER ALLOY
TOP SPRING: STAINLESS
2. CONTACT FINISH: TIN PLATED
3. WIRE SIZE RANGE: 2.5~4.0 MM²
4. CURRENT CARRYING CAPACITY:
UP TO 40 AMPERE (AT 20° C AMBIENT TEMPERATURE)
5. MATING FORCE: 8N MAX
6. CONTACT RESISTANCE: NEW STATE < 2mΩ
7. TAPE REEL PACKING

DIMENSIONS	TOLERANCES	PROJECTION	Amphenol Pcd Shenzhen		TITLE			
ANSI Y14.5M	.X ±0.1		ENGR		2.8MM MALE PIN			
UNITS: MM	.XX ±0.01		ROY.QU 2018.06.18					
Pro/E FILE	ANGLES ±0.5°							
ORIGINAL	THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF AMPHENOL PCD SHENZHEN	CHKD	Derek		SIZE	DWG NO.		REV
		APPD	Eunho		A3	C-C310003611S		B
				CODE: 58982		SCALE: 2:1		SHEET 1 OF 1