


GSD



NOTES:

1. FOR USE WITH M17/119-RG174 & M17/113-RG316 CABLES.
2. FOR CABLING INSTRUCTIONS SEE CP-465.
3. FOR CABLE TRIMMING USE KTJ-116 & KTD-245.
4. FOR CRIMMING USE DIE KTH-2011.
5. INTERFACE PER MIL-STD-348, FIG. 313-1.
6. MATERIALS:
INSULATORS: TEFLON, ASTM-D-1457
K-GRIP SLEEVE: COM. BRONZE TUBE, ALLOY 220
C-RING: PHOSPHOR BRONZE, QQ-B-750
OUTER CONTACT: BER. COPPER, ASTM-B-196
GASKET: SILICONE RUBBER, ZZ-R-765
ALL OTHER METAL PARTS: BRASS, ASTM-B16
7. FINISHES:
CENTER CONTACT: HARD GOLD PLATE, PER MIL-G-45204
ALL OTHER METAL PARTS: SILVER PLATE, PER QQ-S-365
8. ELECTRICAL CHARACTERISTICS:
NOMINAL IMPEDANCE: 50 OHMS
WORKING VOLTAGE: 500 VRMS
FREQUENCY RANGE: DC TO 11 GHz.

GSD

M39012/26-0022

REVISIONS

ISSUE	CHANGES	
	DATE	BY
2	02/05/92	WJM
CN 33709 E REDRAWN		
WJM 02/05/92		
WJM1739		

SCALE 4:1

APPROX SURFACE AREA

125-19-5

USED ON

REF:

PLUG, TNC

DRAWN WJM	DATE 02/05/92
DESIGN MJB	DATE 02/10/92
APPR.	DATE

KINGS
ELECTRONICS CO., INC.
TUCKAHOE, NEW YORK 10707

M39012/26-0022