

PRODUCT DESCRIPTION CODE :

10146061-0XX LF

—RoHS COMPATIBLE

—FOR CUSTOMER CODE:
BLANK = GENERAL USE





—PACKAGING :
BLANK = BULK

—NUMBER OF POSITIONS : 10 TO 30


—MATERIAL

NOTES:

- 1 - MATERIAL:
HIGH TEMPERATURE THERMOPLASTIC
COLOR BLACK UL94 V-0
- 2 - FOR USE WITH MINITEK μ SPACE CTW TERMINALS :
AWG 22-24, SERIES 10141272 & 10148496
AWG 26-30, SERIES 10141272 & 10148496
- 3 - TO BE MATED WITH MINITEK μ SPACE HEADERS SERIES
10146059 / 10146173
- 4 - THE PRODUCT IS NOT INTENDED TO BE EXPOSED TO ANY
SOLDER PROCESS.
- 5 - RoHS COMPATIBLE PRODUCT SPECIFICATIONS
- a - LABELLING :
MEETS PACKAGING SPECS AS PER GS-14-920
- b - LEGAL STATEMENT :
SEE GS-47-0004.




10146061-0XXLF (WITH CPA)




VERSION WITHOUT CPA : OVER REQUEST

PRE-LOAD CONFIGURATION : DELIVERED STATUS


spec ref -				dr		Sawanth, Ambaa	2018/11/26			size	A3	scale	4:1	
tolerance std				eng		Cyril Jeune	2019/07/23			ecn no ELX-F-34299-1				
ISO 406				chr		Hyppias, Arnau	2019/07/24			rel level Released				
ISO 1101				appr		Beatrice Vial	2019/07/24			product family -				
 surface ISO 1302		linear	0.X	±0.3		title	RECEPTACLE ASSEMBLY			dwg no	10146061		rev	B
			0.XX	±0.10										
			0.XXX	±0.005			MINITEK μSPACE STS DR 1.8 TOP LATCH							
		angular	0°	±2°			cat. no. -		Product - Customer Drw			sheet 1 of 3		



PRE-LOAD CONFIGURATION FOR TERMINAL INSERTION




FINAL LOAD CONFIGURATION WITH INSERTED TERMINAL




FULL HEADER AND RECEPTACLE ASSEMBLY CONFIGURATION

PART NO.	NO. OF POSN	DIM "A"
10146061-010LF	10	11.06
10146061-012LF	12	12.86
10146061-014LF	14	14.66
10146061-016LF	16	16.46
10146061-018LF	18	18.26
10146061-020LF	20	20.06
10146061-022LF	22	21.86
10146061-024LF	24	23.66
10146061-026LF	26	25.46
10146061-028LF	28	27.26
10146061-030LF	30	29.06




POSITION NUMBER INDICATION FOR 16POS

spec ref -				dr		Sawanth, Ambaa		2018/11/26		projection		mm		size		A3		scale		5:1											
tolerance std				TOLERANCES UNLESS OTHERWISE SPECIFIED				eng		Cyril Jeune		2019/07/23						ecn no				ELX-F-34299-1									
ISO 406								chr		Hyppias, Arnau		2019/07/24																			
ISO 1101								appr		Beatrice Vial		2019/07/24						product family						-		rel level				Released	
surface ISO 1302 ✓				linear		0.X		±0.3		Amphenol FCi		title		RECEPTACLE ASSEMBLY						dwg no		10146061						rev		B	
						0.XX		±0.10																							
						0.XXX		±0.005																							
MINITEK μSPACE STS DR 1.8 TOP LATCH				cat. no.		-		Product - Customer Drw						sheet 2 of 3																	
angular				0°		±2°																									




TEST PROBE Ø0.4mm COMPLIANCE



HOLE FOR TEST PROBE

DETAIL A
SCALE 20:1



RECOMMENDED LAYOUT OF TEST PROBE Ø0.4mm

spec ref -				dr	Sawanth, Ambaa	2018/11/26	projection	mm	size	A3	scale	8:1
tolerance std				eng	Cyril Jeune	2019/07/23			ecn no ELX-F-34299-1			
ISO 406				chr	Hyppias, Arnau	2019/07/24			rel level Released			
ISO 1101				TOLERANCES UNLESS OTHERWISE SPECIFIED								
ISO 1302				appr	Beatrice Vial	2019/07/24	product family -					
surface	linear	0.X	±0.3	Amphenol FCI	title RECEPTACLE ASSEMBLY			dwg no	10146061			rev B
		0.XX	±0.10									
		0.XXX	±0.005									
ISO 1302		angular	0°	±2°	cat. no. -			Product - Customer Drw			sheet 3 of 3	