


NOTES:

- 1) LABELS ARE M23053/5 ,WHITE. ACCEPTABLE SUBSTITUTION IS DAT-38-292 OR TRANSVINYL (DAT-63-292-2.5).
- 2) TERMINUS ENFACE REQUIREMENTS SHALL MEET GR-326 AND IEC 61300-3-35.
- 3) MAX IL @ 850 nm SHALL BE 0.5 dB PER CONNECTION.

REVISION HISTORY - ALL SHEETS ARE AT THE SAME REVISION			
REV	DESCRIPTION	DATE	APPROVED
-	INITIAL RELEASE	2017/11/13	



4	AFSI-PRE T BOX	BOX, SMALL FIBER CABLE 10X10X2 W/AFSI GRAPHICS	1
3	SE001L202C0E-BI	CABLE, 2.0mm 50um OM3 BEND INSENSITIVE P/N: SE001L202C0E-BIF	3.78 FEET
2	MSTC1100	ST CONNECTOR, MM 128UM (COMMERCIAL)	1
1	M29L1000	TERMINUS, SOC, M29504/05-4046 MM,.127MM, +.002/-0 FIBER HOLE	1
ITEM NO.	PART NO.	DESCRIPTION	QTY/ LENGTH

		MATERIAL:	DFT/Designer:	C. Hoang	2017/10/23						
			Check By:	B. Waite	2017/10/24						
			Manufacturing:	B. Waite	2017/10/24						
			DRILLED HOLE DIAMETER TOLERANCE	Market Manager/PLM:	Q. Abraham	2017/10/25	TITLE: M29504/5 SOCKET TO ST CABLE ASSEMBLY, MM, 62.5/125um				
			Ø.000 TO Ø.125 $\pm .001$ Ø.126 TO Ø.250 $\pm .001$ Ø.251 TO Ø.500 $\pm .001$ Ø.501 TO Ø.750 $\pm .001$	Configuration Management:	L. Brown	2017/11/13					
		DO NOT SCALE DRAWING UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOL ON ANGLES ±3° 1 PL ±.1 2 PL ±.02 3 PL ±.010 INTERPRET DIM AND TOL PER ASME 14.5M-1994	This Document contains proprietary information and such information is prohibited from disclosure to others, publication or duplication in whole or in part without written permission from Amphenol Fiber Systems International. Copyright © 2017 Amphenol Fiber Systems International. Non published work. All rights reserved.			SIZE	CAGE CODE	DWG NO	REV		
NEXT ASSY	USED ON		A			OYPM2	2016022306AS-D2		-		
APPLICATION			SCALE: NONE			SHEET 1 OF 1					