

PRODUCT DESCRIPTION CODE :

10156818-A002 LF

RoHS COMPATIBLE

FOR CUSTOMER CODE:
BLANK = GENERAL USE

PACKAGING :
BLANK = BULK

NUMBER OF POSITIONS : 02

MATERIAL (SEE NOTE 1)

CODING TYPE :

BLANK = NEUTRAL BLACK COLOR

A = CODING A BLACK COLOR

B = CODING B BLACK COLOR

C = CODING B NATURAL COLOR

NOTES:

1 - MATERIAL :
HIGH TEMPERATURE THERMOPLASTIC UL94 V-0

2 - PACKAGING : BULK





3 - FOR USE WITH MINITEK μ SPACE CTW TERMINALS :
AWG 26-30, SERIE 10141272

4 - TO BE MATED WITH MINITEK μ SPACE HEADERS SERIES
10156816 & 10159449


5 - RoHS COMPLIANT, THE PRODUCT IS NOT INTENDED TO BE
EXPOSED TO ANY SOLDER PROCESS.


6 - PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHERS
COUNTRY REGULATIONS AS PER GS-022-008

7 - VIEWS WITHOUT NAME CORRESPOND TO THE NEUTRAL CODING




PRE-LOAD CONFIGURATION : DELIVERED STATUS


spec ref -				dr Ramu P		2020/02/25		projection				mm		size A3		scale 5:1	
tolerance std				eng Moisan, Gwenda		2020/11/16				ecn no ELX-F-38970-1		rel level Released					
ISO 406				chr -		-											
ISO 1101				appr Cyril Jeune		2020/11/17											
surface				linear		0.X		±0.3		Amphenol FCI		title RECEPTACLE ASSEMBLY		dwg no 10156818		rev B	
						0.XX		±0.10									
						0.XXX		±0.05									
						0°		±2°									
ISO 1302				angular		0°		±2°		cat. no.		Product - Customer Special Drw				sheet 1 of 3	




PRE-LOAD CONFIGURATION FOR TERMINAL INSERTION




2POS NEUTRAL CODING




2POS CODA DIMENSIONS




2POS CODB DIMENSIONS




FINAL LOAD CONFIGURATION WITH INSERTED TERMINAL




FULL HEADER AND RECEPTACLE ASSEMBLY CONFIGURATION




POSITION NUMBER INDICATION


spec ref -				dr		Ramu P	2020/02/25	projection 	mm 	size	A3	scale	5:1	
tolerance std				eng		Moisan, Gwenda	2020/11/16			ecn no				ELX-F-38970-1
ISO 406 ISO 1101				chr		-	-			rel level				Released
				appr		Cyril Jeune	2020/11/17	product family						
surface  ISO 1302		linear	0.X	±0.3	Amphenol FCi	title RECEPTACLE ASSEMBLY MINITEK μSPACE STS 1.5 TOP LATCH				dwg no 10156818		rev B		
			0.XX	±0.10										
			0.XXX	±0.05										
		angular	0°	±2°			cat. no.		Product - Customer Special Drw			sheet 2 of 3		



TEST PROBE $\varnothing 0.4\text{mm}$ COMPLIANCE



RECOMMENDED LAYOUT OF TEST PROBE $\varnothing 0.4\text{mm}$



spec ref -				dr		Ramu P	2020/02/25	projection	mm	size	A3	scale	2:1
tolerance std ISO 406 ISO 1101	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng		Moisan, Gwenda	2020/11/16			ecn no	ELX-F-38970-1		
				chr		-	-						
				appr		Cyril Jeune	2020/11/17			product family			rel level
surface ISO 1302	linear	0.X	±0.3	Amphenol FCi	title RECEPTACLE ASSEMBLY			dwg no	10156818			rev B	
		0.XX	±0.10										
		0.XXX	±0.05		MINITEK μSPACE STS 1.5 TOP LATCH								
	angular	0°	±2°	cat. no.					Product - Customer Special Drw				sheet 3 of 3