


REV	DESCRIPTION	DATE	APP
J	ECN 161205-1105, XLT	2016/12/06	CJ


- 3 TORQUE INSERT CAP SCREWS TO 4.75±.25 IN.-LBS.

EXAMPLE: FS4H6000-6A13 DESCRIBES:
RECEPTACLE ASSY, FLANGE, EXTERNAL MOUNT, TFOCA-II® 4CH WITH:
6061-T6 Zn-ALLOY COLOR OD,
NITRILE ORINGS / FLUOROSILICONE NON-CONDUCTIVE PANEL SEAL (GASKET),
KEY OPTION 1,
DUST CAP STYLE FEMALE

1




PANEL CUT-OUT DIMENSIONS




KEY OPTION 1




KEY OPTION 2




KEY OPTION 3




KEY OPTION
UNIVERSAL



KEY OPTION 5



QUICK LINK, KEY 1
OPTION 6



QUICK LINK, KEY 2
OPTION 7

VIEW A-A
SCALE: 3/1

SIZE	CAGE CODE	DWG NO	REV
C	ØYPM2	FS4H6000	J
SCALE	SHEET	2 OF 2	
2:1	1		