


NOTES:

- 1) LABEL REQUIREMENT:
LABELS ARE M23053/5, WHITE. ACCEPTABLE SUBSTITUTION IS DAT-38-292 OR TRANSVINYL (DAT-63-292-2.5).
LOCATE APPROXIMATELY AS SHOWN.
- 2) TERMINUS ENDFACE REQUIREMENTS SHALL MEET GR-326 AND IEC 61300-3-35.
- 3) MAX IL @ 1310 nm SHALL BE 0.5 dB PER CONNECTION.

REVISION HISTORY - ALL SHEETS ARE AT THE SAME REVISION			
REV	DESCRIPTION	DATE	APPROVED
-	INITIAL RELEASE	2017/11/13	



7	AFSI-PRE T BOX	BOX, SMALL FIBER CABLE 10X10X2 W/AFSI GRAPHICS	1
6	WTRO-0200	CABLE, 2 FIBER 9/125 TACTICAL BREAKOUT	3.25 FEET
5	BLCC1588709-1	CONNECTOR KIT, LC, SIMPLEX, SM JUMPER, 1.6-2.0MM	2
4	202K121-25-0	SHRINK BOOT, RAYCHEM	1
3	M85049/69-11W	BACKSHELL SHRINK BOOT ADAPTER	1
2	M801-SU2N	ARINC 801 TERMINI, UPC, NON-PULL PROOF	2
1	FS801-11P02ACN	PLUG ASSEMBLY, ARINC, SH 11	1
ITEM NO.	PART NO.	DESCRIPTION	QTY/ LENGTH

P1	PINOUT DIAGRAM	B LABEL INFORMATION
A		A
B		B

				MATERIAL:	DFTR/Designer: C. Hoang	2017/10/20					
					Check By: B. Waite	2017/10/24					
					Manufacturing: B. Waite	2017/10/24					
				DRILLED HOLE DIAMETER TOLERANCE	Market Manager/PLM: Q. Abraham	2017/10/25	TITLE: 2 CHANNEL ARINC PLUG TO LC ASSEMBLY, SM				
				Ø.000 TO Ø.125 ^{+0.001} / _{-.001} Ø.251 TO Ø.500 ^{+0.002} / _{-.001} Ø.126 TO Ø.250 ^{+0.002} / _{-.001} Ø.501 TO Ø.750 ^{+0.003} / _{-.001}	Configuration Management: L. Brown	2017/11/13					
				DO NOT SCALE DRAWING UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOL ON ANGLES 13° 1 PL ±.1 2 PL ±.02 3 PL ±.010	This Document contains proprietary information and such information is prohibited from disclosure to others, publication or duplication in whole or in part without written permission from Amphenol Fiber Systems International. Copyright © 2017 Amphenol Fiber Systems International. Non published work. All rights reserved.						
				INTERPRET DIM AND TOL PER ASME 14.5M-1994							
NEXT ASSY		USED ON						SIZE	CAGE CODE	DWG NO	REV
								A	0YPM2	16032202MD-D2	-
APPLICATION								SCALE: NONE			SHEET 1 OF 1