



EXPORT CONTROLLED
THIS DOCUMENT CONTAINS TECHNICAL DATA AS DERIVED BY THE EXPORT ADMINISTRATION REGULATIONS, AND IS SUBJECT TO THE EXPORT CONTROL LAWS OF THE U.S. GOVERNMENT.
ECCN **EAR99**

- Ø84 CABLE
- FOUR CONDUCTOR
- O.D. .210 inches
- JACKET COLOR BLACK
- MINIMUM BEND RADIUS 0.312 inches
- WORKING TEMP RANGE -40° TO 80°C
- MUTUAL CAPACITANCE (Ø1KHz) 48 pF/ft
- PN-OUT:
- RM12S CABLE R2-2-2
- 1 GREEN CHANNEL X
- 2 RED CHANNEL Y
- 3 WHITE CHANNEL Z
- 4 BLACK CHANNEL X,Y,Z SHELLS
- N/C SHIELD CHANNEL X,Y,Z SHELLS

PROPRIETARY
THIS DOCUMENT IS ISSUED IN STRICT CONFIDENCE ON CONDITION THAT IT IS NOT COPIED, REPRINTED, OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT PRIOR WRITTEN CONSENT OF WILCOXON SENSING TECHNOLOGIES.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES.

DR P. EITNER

DATE 07/26/23

DRG

DATE

COMPT

DATE

DO NOT SCALE DRAWING

TOLERANCES:
XX = ± .01
X = ± .5

DRG

DATE

QA

DATE

APPR

DATE

WILCOXON SENSING TECHNOLOGIES

8435 Progress Dr.
Breadeaford, MD 21701 USA

SCALE NONE

SHEET 1 OF 1

REV. NO. 01

REV. 01

EXPORT CONTROLLED
THIS DOCUMENT CONTAINS TECHNICAL DATA AS DERIVED BY U.S. EXPORT REGULATIONS AND IS SUBJECT TO THE EXPORT CONTROL LAWS OF THE U.S. GOVERNMENT. CONTACT WILCOXON SENSING TECHNOLOGIES TO OBTAIN SPECIFIC EXPORT CONTROL CLASSIFICATION.