


Amphenol PCDSZ
ORIGINAL
PDF Format
R&D

REV	ECN	DESCRIPTION	DATE	MODIFIED
1		PRE-RELEASE	2019.9.23	Celine.xie





安费诺精密连接器(深圳)有限公司
Amphenol PCD Shenzhen

受 控 文 件

2019年9月24日

NOTES/备注:

- ★ 1. TERMINAL : COPPER ALLOY , PIN CAP : PA66+GF25
端子：铜合金，针帽：PA66+GF25
- 2. CURRENT TERMINAL(BUS-BAR(STANDARD THREAD M8)
SET SCREW LOCKING TORQUE IS 15N.m Max
M8建议的锁紧扭力最大15N.m
- ★ 3. RoHS COMPLIANCE/满足RoHS
- ★ CRITICAL CHARACTERISTIC MARKS/关键特性符号

DIMENSIONS	TOLERANCES	PROJECTION	Amphenol Pcd Shenzhen		TITLE 10 MM PIN CONTACT ASSEMBLY			
ANSI Y14.5M UNITS: MM Pro/E FILE	.X ±0.5 .XX ±0.05 ANGLES ±0.5°		ENGR Celine.xie 2019.9.23					
ORIGINAL NOT FOR CUSTOMER DISTRIBUTION	THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF AMPHENOL PCD SHENZHEN		CHKD 	SIZE A3	DWG NO. C-C4200036152		REV 1	
			APPD 	CODE: 58982		SCALE: 1:1	SHEET 1 OF 1	