



THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.


CUSTOMER DRAWING

REVISIONS					
REV#	ECR	REVISION ACTION	REV.BY:	APPR.BY:	DATE
A		INITIAL RELEASE	LQ	JL	06/09/2022


Amphenol TPI
2022-06-09
REGISTERED COPY



剖面 A-A
比例 5:1




剖面 B-B
比例 5:1



注(NOTES):

1. 对配公端直径 Mating contact diameter: 1.0mm
2. 额定电流 Current rating: 5A
3. 端子类型 Terminatin type: Crimp
4. 压线规格 Wire size: AWG20~22
5. 电镀信息 Plating specification:
镍底 镀锡
Tin over nickel
6. 材料规格 Material specification:
6.1. 端子: 铜合金 Contact body: Copper alloy
6.2. 外套: 不锈钢 Outer spring: Stainless steel
7. 符合ROHS ROHS compliant



Amphenol Technical Products International Asia.

第三角投影 THIRD ANGLE PROJECTION	页面 SHEET	幅面 SIZE	版次 REV.	比例 SCALE	PART NAME:	
	1 OF 1	A4	A		HC Contact 20# Skt 20-22AWG	
UNLESS OTHERWISE SPECIFIED					DWG NO:	
1) All dimensions are in metric(mm). 2) Tolerances are as follows: 1. PL DEC ± 1.00 2. PL DEC ± 0.50 3. PL DEC ± 0.20					HCTF20104	
Angles ±1°					CUST PART #	CUST REV.
					N/A	A



Key	Signature	Date
Characteristics Critical	制图 DRAWN	LQ
Amphenol for Latest Definition	审核 CHECKED	6/9/2022
	批准 APPROVAL	6/9/2022

THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.


CUSTOMER DRAWING

REVISIONS


REV#	ECR	REVISION ACTION	REV.BY:	APPR.BY:	DATE
A		INITIAL RELEASE	LQ	JL	06/09/2022



剖面 A-A
比例 5:1




剖面 B-B
比例 5:1



注(NOTES):

- 对配公端直径 Mating contact diameter:1.0mm
- 额定电流 Current rating: 5A
- 端子类型 Terminatin type: Crimp
- 压线规格 Wire size: AWG20~22
- 电镀信息 Plating specification:
镍底, 镀锡
Tin over nickel
- 材料规格 Material specification:
6.1. 端子: 铜合金 Contact body: Copper alloy
6.2. 外套: 不锈钢 Outer spring: Stainless steel
7. 符合ROHS ROHS compliant



Amphenol Technical Products International Asia.

第三角投影 THIRD ANGLE PROJECTION	页面 SHEET	幅面 SIZE	版次 REV.	比例 SCALE	PART NAME:
	1 OF 1	A4	A		HC Contact 20# Skt 20-22AWG
签名 SIGNATURE	日期 DATE	UNLESS OTHERWISE SPECIFIED 1) All dimensions are in metric(mm). 2) Tolerances are as follows: 1.PL DEC ± 1.00 2.PL DEC ± 0.50 3.PL DEC ± 0.20 Angles ±1°			
制图 DRAWN	LQ	06/09/2022	DWG NO: HCTF20104		
审核 CHECKED			CUST PART # N/A		
批准 APPROVAL			CUST REV. A		

Key Characteristics Critical	定义 Definition
Amphenol for Latest	重点特性 Significant