





RoHS Compliant

| Rev.                                           | SIGN | DATE       | DESCRIPTION       | APPROVER |
|------------------------------------------------|------|------------|-------------------|----------|
| B                                              | —    | 2024.05.13 | The first release | Guoxue   |
| THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!! |      |            |                   |          |



SECTION A-A



PCB Layout

Technical Specification:

1. Material: Copper alloy,Matte Tin Plated.
2. Current: 80A.
3. Torque: 10 lbf.in.
- 4.Mark "▲" is the Critical dimension.

**Amphenol**  
**ANYTEK**

**CUSTOMER COPY**

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUTWRITTEN AUTHORITY FROM THE PROPRIETOR.PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

| TITLE    |         | AMT44005 Conductive Bracket |                      |                                                                                       |            |
|----------|---------|-----------------------------|----------------------|---------------------------------------------------------------------------------------|------------|
| PART NO. |         | AMT0440005TH0000G           |                      | DWG NO.                                                                               | 8AMT0009   |
| APPROVED | CHECKED | DESIGNED                    | DRAWN                | CUST NO.                                                                              |            |
|          |         | Guoxue<br>2024.05.13        | Guoxue<br>2024.05.13 |  | Tolerance  |
|          |         |                             |                      |                                                                                       | >30 ±0.60  |
|          |         |                             |                      |                                                                                       | 6-30 ±0.40 |
|          |         |                             |                      |                                                                                       | 0-6 ±0.30  |
|          |         |                             |                      |                                                                                       | ANGLES ±1° |
|          |         |                             |                      | SHEET: 01/01                                                                          | REV.: B    |