

JAND38999/33 RECEPTACLE CAPS

MIL-DTL-38999 Series III

Connector Group L

JAND38999/33	W	15	R
Designates Receptacle Dust Cover	MATERIALS & FINISH	ACCESSORY SHELL SIZE	STYLE
	W: Aluminum Alloy/Cadmium	9	N: W/ SS Rope & Ring R: W/ SS Rope C : Cover only
	Z: Aluminum Alloy/ Black Zinc Nickel	11	
	F: Aluminum Alloy/ Electroless Nickel	13	
	K: Stainless Steel/Passivated	15	
	N: Stainless Steel/ Electrodeposited Nickel	17	
		19	
		21	
		23	
		25	




TABLE A

Accessory Shell Size	A Ø		B Ø Max.		C Ø Min.		D Ø Max.		L	
									+13.00/-7.00	
	mm	inch	mm	inch	mm	inch	mm	inch	mm	inch
9	15.74	0.62	23.0	0.90	27.0	1.06	17.64	0.69	127.00	5
11	19.05	0.75	28.0	1.10	32.0	1.25	21.97	0.86	127.00	5
13	22.09	0.87	31.0	1.22	37.0	1.45	25.12	0.98	127.00	5
15	25.4	1.00	32.0	1.25	40.0	1.57	29.92	1.17	127.00	5
17	29.97	1.18	37.0	1.45	44.0	1.73	32.0	1.25	127.00	5
19	31.75	1.25	39.0	1.53	46.0	1.81	36.27	1.42	127.00	5
21	34.79	1.37	42.0	1.65	49.0	1.92	38.25	1.50	127.00	5
23	38.1	1.50	45.0	1.77	54.0	2.12	42.62	1.67	127.00	5
25	41.14	1.62	49.0	1.92	56.0	2.20	44.45	1.75	127.00	5

JAND38999/32 PLUG CAPS

MIL-DTL-38999 Series III

Connector Group L

JAND38999/32	W	15	R
Designates Plug Dust Cover	MATERIALS & FINISH	ACCESSORY SHELL SIZE	STYLE
	W: Aluminum Alloy/Cadmium	9	N: W/ SS Rope & Ring R: W/ SS Rope C ` Cover only
	Z: Aluminum Alloy/ Black Zinc Nickel	11	
	F: Aluminum Alloy/ Electroless Nickel	13	
	K: Stainless Steel/Passivated	15	
	N: Stainless Steel/ Electrodeposited Nickel	17	
		19	
		21	
		23	
		25	




TABLE A														
Accessory Shell Size	A Ø		B Ø Max.		C Ø Min.		D Ø Max.		E Ø Min.		F		L	
													+13.00/-7.00	
	mm	inch	mm	inch	mm	inch	mm	inch	mm	inch	mm	inch	mm	inch
9	15.74	0.62	17.20	0.68	12.50	0.49	24.00	0.94	13.00	0.51	24.00	0.95	127.00	5.00
11	19.05	0.75	20.50	0.81	15.75	0.62	27.00	1.06	18.00	0.71	20.50	0.81	127.00	5.00
13	22.09	0.87	24.30	0.96	19.53	0.77	30.00	1.18	20.00	0.79	27.00	1.06	127.00	5.00
15	25.4	1.00	27.40	1.08	22.71	0.89	31.00	1.22	23.00	0.91	22.50	0.89	127.00	5.00
17	29.97	1.18	30.60	1.20	25.88	1.018	37.00	1.46	26.00	1.02	30.50	1.20	127.00	5.00
19	31.75	1.25	33.25	1.31	28.55	1.12	40.00	1.57	29.00	1.14	31.50	1.24	127.00	5.00
21	34.79	1.37	36.40	1.43	31.72	1.248	44.00	1.73	32.00	1.26	33.00	1.30	127.00	5.00
23	38.1	1.50	39.70	1.56	34.90	1.37	46.00	1.81	34.00	1.34	34.00	1.34	127.00	5.00
25	41.14	1.62	42.80	1.69	38.07	1.50	49.00	1.92	39.00	1.54	38.00	1.50	127.00	5.00