

JAND38999/32 COMPOSITE PLUG

MIL-DTL-38999 Series III

JAND38999/32	W	15	R
SERIES	FINISH	SHEL SIZE	STYLES
	J- Composite, Cadmium Olive Drab M- Composite, Electroless Nickel	9 11 13 15 17 19 21 23 25	N - With S.S. Rope & Ring R - With S.S. Rope C - Cover only.




TABLE-A														
SHELL SIZE	A THREAD 2A -0.1 P--0.3L-T5		ØB		C		ØD MAX		ØE MIN		F MAX/MIN		L MAX	
			+ 0.0 - 0.30		+ 0.0 - 0.15								+ 13.0 - 7.0	
	inch		inch	mm	inch	mm	inch	mm	inch	mm	inch	mm	inch	mm
9	0.625	15.875	0.68	17.20	0.49	12.50	0.94	24.0	0.51	12.95	0.94\0.57	24.0\14.5	5.0	127.0
11	0.750	19.05	0.81	20.50	0.62	15.75	1.06	27.0	0.71	18.03	0.81\0.71	20.5\18.0	5.0	127.0
13	0.875	22.225	0.96	24.30	0.77	19.53	1.18	30.0	0.79	20.07	1.06\0.79	27.0\20.0	5.0	127.0
15	1.000	25.4	1.08	27.40	0.89	22.71	1.22	31.0	0.91	23.11	0.89\0.71	22.5\18.0	5.0	127.0
17	1.1875	30.1625	1.20	30.60	1.02	25.88	1.46	37.0	1.02	25.91	1.20\0.93	30.5\23.5	5.0	127.0
19	1.250	31.75	1.31	33.25	1.12	28.55	1.57	40.0	1.14	28.96	1.24\0.98	31.5\25.0	5.0	127.0
21	1.375	34.925	1.43	36.40	1.25	31.72	1.73	44.0	1.26	32.00	1.30\1.04	33.0\26.5	5.0	127.0
23	1.500	38.1	1.56	39.70	1.37	34.90	1.81	46.0	1.34	34.04	1.34\1.08	34.0\27.5	5.0	127.0
25	1.625	41.275	1.69	42.80	1.50	38.07	1.93	49.0	1.54	39.12	1.50\1.18	38.0\30.0	5.0	127.0

JAND38999/33 COMPOSITE RECEPTACLE

MIL-DTL-38999 Series III

JAND38999/33	W	15	R
SERIES	FINISH	SHEL SIZE	STYLES
	J- Composite, Cadmium Olive Drab M- Composite, Electroless Nickel	9 11 13 15 17 19 21 23 25	N - With S.S. Rope & Ring R- With S.S. Rope C - Cover only.




TABLE A												
Accessory Shell Size	A Ø		B Ø Max.		C Ø Min.		D Ø Max.		E Msx./Min.		L	
	mm	inch	mm	inch	mm	inch	mm	inch	mm	inch	mm	inch
9	15.74	0.62	23.0	0.90	27.0	1.06	17.64	0.69	21.0\18.0	0.83\0.71	127.00	5
11	19.05	0.75	28.0	1.10	32.0	1.25	21.97	0.86	22.5\18.5	0.89\0.73	127.00	5
13	22.09	0.87	31.0	1.22	37.0	1.45	25.12	0.98	25.0\23.5	0.98\0.93	127.00	5
15	25.4	1.00	32.0	1.25	40.0	1.57	29.92	1.17	31.0\25.0	1.22\0.98	127.00	5
17	29.97	1.18	37.0	1.45	44.0	1.73	32.0	1.25	32.5\26.5	1.28\1.04	127.00	5
19	31.75	1.25	39.0	1.53	46.0	1.81	36.27	1.42	34.0\28.0	1.34\1.10	127.00	5
21	34.79	1.37	42.0	1.65	49.0	1.92	38.25	1.50	35.5\30.0	1.40\1.18	127.00	5
23	38.1	1.50	45.0	1.77	54.0	2.12	42.62	1.67	37.5\31.5	1.48\1.24	127.00	5
25	41.14	1.62	49.0	1.92	56.0	2.20	44.45	1.75	39.0\33.0	1.54\1.30	127.00	5