

This document is the property of Amphenol Corporation and is delivered on the express condition that is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, and that no right is granted to disclose or to use any information in this document.

The marking on this product doesn't contain environmental hazardous materials per directive 2011/65/EU & 2015/863/EU for RoHS compliant and per IEC 61249-2-21 for Halogen-Free compliant.

FOR REFERENCE ONLY



REVISIONS				
SYM	ECN No.	DESCRIPTION	DATE	BY
AX1	EDSR#8738	NON-RELEASE REVISION	11/26/2018	Roger Tsai
AX2		UPDATE DRAWING AND PACKING	01/31/2020	Roger Tsai
AX3		UPDATE PCB MISTAKE DIM	2021-08-12	Debby Hung

NOTES:

1. MATERIAL:

HOUSING: LCP, UL94V-0, COLOR: OPTIONS.
CONTACT: BRASS.
SHELL: SPCC.
BOARD LOCK: BRASS.





2. FINISH:

TERMINAL:
CONTACT AREA: SELECTED GOLD PLATING;
SOLDERING AREA: MATTE TIN PLATING 100 μ " THICKNESS MIN.;
UNDER PLATING: NICKEL PLATING 50 μ " THICKNESS MIN. OVERALL.
SHELL:
ELECTROLESS NICKEL PLATING 50 μ " THICKNESS MIN. OVERALL.
BOARD LOCK:
BRIGHT TIN PLATING 100 μ " THICKNESS MIN.;
UNDER PLATING: NICKEL PLATING 50 μ " THICKNESS MIN. OVERALL.

3. PRODUCT SPECIFICATION REFER TO : PS-7680

4. SCREW LOCKING FORCE: 3.0 KGF-CM MAX.

5. THIS PRODUCT DOESN'T CONTAIN ENVIRONMENTAL HAZARDOUS
PER DIRECTIVE 2011/65/EU & 2015/863/EU FOR RoHS COMPLIANT.
AND PER IEC 61249-2-21 FOR HALOGEN-FREE COMPLIANT.



PART NO. G12B1 X 10 X X OFHR

CONTACT FINISH
0: GOLD FLASH
2: 30 μ " GOLD
3: 15 μ " GOLD

TAIL LENGTH(DIM L):
2: 2.75mm

COLOR OPTION
1: IVORY
2: BLACK

TOLERANCE		APPROVALS		DATE	TITLE			Amphenol®		
X. X.X ±0.30 X.XX ±0.20 X.XXX ±0.10		DRAWN Debby Hung	2021-08-12	DVI RECEPTACLE, VT PCB MOUNT 24+5 POS. DIP TYPE			Amphenol Corporation Amphenol Taiwan Corporation			
		CHECKED Sandy Wu	2021-08-12							
		APPROVED Roger Tsai	2021-08-12							
ANGULAR ±1°						UNIT mm	SIZE A3	PART No. G12B1X10XXOFHR		
UNLESS OTHERWISE SPECIFIED		DWG TYPE CUST DWG	PROJECT CODE SKT			SCALE NA	SHEET 1 OF 2	DWG No. G12B1X10XXOFHR	REV. AX3	


This document is the property of Amphenol Corporation and is delivered on the express condition that is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, and that no right is granted to disclose or to use any information in this document.

The marking on this product doesn't contain environmental hazardous materials per directive 2011/65/EU & 2015/863/EU for RoHS compliant and per IEC 61249-2-21 for Halogen-Free compliant.

FOR REFERENCE ONLY



REVISIONS				
SYM	ECN No.	DESCRIPTION	DATE	BY
AX1	EDSR#8738	NON-RELEASE REVISION	11/26/2018	Roger Tsai
AX2		UPDATE DRAWING AND PACKING	01/31/2020	Roger Tsai
AX3		UPDATE PCB MISTAKE DIM	2021-08-12	Debby Hung



TOLERANCE		APPROVALS		DATE		TITLE		Amphenol® Amphenol Corporation Amphenol Taiwan Corporation	
X.		DRAWN	Debby Hung	2021-08-12		DVI RECEPTACLE, VT PCB MOUNT 24+5 POS. DIP TYPE		Part No. G12B1X10XX0FHR G12B1X10XX0FHR	
X.X	±0.30	CHECKED	Sandy Wu	2021-08-12					
X.XX	±0.20	APPROVED	Roger Tsai	2021-08-12					
X.XXX	±0.10							DWG No. G12B1X10XX0FHR	
ANGULAR	±1°	DWG TYPE	CUST DWG	PROJECT CODE	SKT				
UNLESS OTHERWISE SPECIFIED						UNIT	mm	SIZE	A3
						SCALE	NA	SHEET	2 OF 2

PACKAGING
BY TRAY

9.82
G/W
KG

7.44
N/W
KG

50
PCS/
TRAY

24
TRAYS/
BOX

1200
QUANTITY
(PCS)

G12B1X10XX0FHR
PART NUMBER