




THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.

CUSTOMER DRAWING


REVISIONS					
REV#	ECR	REVISION ACTION	REV.BY:	APPR.BY:	DATE
A		INITIAL RELEASE	LQ	JL	04/03/2022



剖面 A-A
比例 5:1



剖面 B-B
比例 5:1



注(NOTES):

- 对配公端直径 Mating contact diameter: 1.6mm
- 额定电流 Current rating: 13A
- 端子类型 Terminatin type: Crimp
- 压线规格 Wire size: AWG16~18
- 电镀信息 Plating specification:
镍底, 整个端子镀金.
Gold flash plate overall.
- 材料规格 Material specification:
6.1. 端子: 铜合金 Contact body: Copper alloy
6.2. 外套: 不锈钢 Outer spring: Stainless steel
- 符合ROHS ROHS complian



Amphenol Technical Products International Asia.

第三角投影 THIRD ANGLE PROJECTION	页 面 SHEET	幅 面 SIZE	版 次 REV.	比 例 SCALE	PART NAME:
	1 OF 1	A4	A		HC Contact 16#Socket 16~18AWG
签名 SIGNATURE	日期 DATE	UNLESS OTHERWISE SPECIFIED			DWG NO:
制 图 DRAWN	LQ	1) All dimensions are in metric (mm). 2) Tolerances are as follows:			HCTF16161
审 核 CHECKED	JL	1. PL DEC ± 1.00 2. PL DEC ± 0.50 3. PL DEC ± 0.20			CUST PART #
批 准 APPROVAL		Angles ± 1°			N/A
					CUST REV. A

Key	Characteristics	Critical
Contact	Amphenol for	Latent
Definition	Significant	重点特性