






V1 FILAMENT:
 5.2-5.5 VDC
 FILAMENT CURRENT:
 45 +/- 10 mA DC
 V2 ELECTRODE SOURCE:
 24-26 VDC TYP.
 ELECTRODE CURRENT:
 14 +/- 3.0 mA DC
 BALLAST RESISTOR:
 1K TYP.
 ELECTRODE RUNNING VOLTAGE:
 10 +/- 3.0 V DC
 TOTAL LAMP WATTAGE:
 .40 TYP.
 INTENSITY
 .1mW/Cm² @ 365nm
 LIFE HOURS:
 *15,000

*TO 50% OUTPUT INTENSITY



JKL PART NO.: BGF717-UV1

			METRIC  THIRD ANGLE PROJECTION		DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0.20 ANGLE +/- 0		JKL COMPONENTS CORPORATION					
							TITLE MINIATURE HOT CATHODE FLUORESCENT UV LAMP (ACORN)					
			DRAWN BY		APPV'D BY DATE		SIZE	FSCM NO.	DRAWING NO.			
			L. WENGSTROM		F.D. 5/9/01		A	55335	BGF717-UV1			
RELEASED AND CANCEL P-9911-03			5/9/01									
REV. NO.	DESCRIPTION/ECO NUMBER		APPV'D DATE	- CAD DRAWING -			SCALE	RELEASED DATE		REVISION DATE	REV. NO.	SHEET 1 OF 1
				MANUAL REVISIONS NOT PERMITTED			NONE	5/9/01				