





PRODUCT DATA DRAWING

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
-	DCN 41643	09/15	DAL




RECOMMENDED MOUNTING HOLE

MATERIAL:

BODY & LOCKWASHER:	BRASS PER ASTM B16, ALLOY UNS No. C36000
CONTACT:	BERYLLIUM COPPER PER ASTM B196, ALLOY No. UNS C17300, TD04
INSULATOR:	PTFE PER ASTM D1710, TYPE I, GRADE 1, CLASS B
LOCKWASHER:	PHOSPHOR BRONZE PER ASTM-B 103, ALLOY 52100
FINISH:	
BODY, HEX NUT & LOCKWASHER::	SILVER PER ASTM B700, TYPE , GRADE D, CLASS S (.00020-.00030) WITH TARNISHING PROTECTION
CONTACT:	GOLD PER ASTM B488, TYPE II, CODE C, CLASS 1.27, OVER NICKEL PER AMS-QQ-N-290, CLASS 1, .00005" MIN.

PERFORMANCE:

IMPEDANCE:	50 OHMS
------------	---------

MATERIAL:	SEE NOTES	DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL: ±1/64 ANGULAR: X° ±1°0' X°X' ±15' DECIMAL: .X ±.030 .XX ±.010 .XXX ±.005 INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994	UNLESS OTHERWISE SPECIFIED 1) ALL DIMENSIONS ARE IN INCHES (MILLIMETERS) 2) ALL DIMENSIONS ARE AFTER PLATING. 3) BREAK CORNERS & EDGES .005 R. MAX. 4) CHAM. 1ST & LAST THREADS. 5) SURFACE ROUGHNESS 63-MIL-STD-10. 6) DIA.'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R. 7) REMOVE ALL BURRS	 2400 Centrepark West Drive, Suite 100 West Palm Beach, FL 33409	
FINISH:	SEE NOTES			TITLE: TNC BULKHEAD JACK JAM-NUT MOUNT WITH SOLDER POT	
SURFACE AREA:	N/A			SIZE: B CAGE CODE: 95077 DWG. NO.: M39012/31-0002	
PROPRIETARY THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED.		THIRD ANGLE PROJECTION 	DRAWN: GPF 09/11/15	SCALE: 4:1	
			CHECKED: DAL 09/11/15		
			APPROVED: DAL 09/11/15	SHEET 1 OF 1	