





RoHS Compliant



Poles	2x2	2x3	2x4	2x5	2x6	2x7	2x8	2x9	2x10	2x11	2x12	2x13
Dim L	10.16	15.24	20.32	25.40	30.48	35.56	40.64	45.72	50.80	55.88	60.96	66.04
Dim B	5.08	10.16	15.24	20.32	25.40	30.48	35.56	40.64	45.72	50.80	55.88	60.96
TOL	±0.15					±0.25						±0.35
Poles	2x14	2x15	2x16	2x17	2x18	2x19	2x20	2x21	2x22	2x23	2x24	
Dim L	71.12	76.20	81.28	86.36	91.44	96.52	101.60	106.68	111.76	116.84	121.92	
Dim B	66.04	71.12	76.20	81.28	86.36	91.44	96.52	101.60	106.68	111.76	116.84	
TOL	±0.35					±0.40						

Rev	SIGN	DATE	DESCRIPTION	APPROVER
C	△	2009.01.08	Terminal screw changed from M2.5 to M3.0	Kind
	△	2009.01.08	Safety Approval:cULus	Kind
D	△	2010.11.06	Construction is change	Aaron
E	△	2018.12.03	Change the Wave soldering temperature from 250°C±10°C/5 Sec to 260°C±5°C/5 Sec	ZHENBIN
	△	2018.12.03	Change the dimension from 9.5mm to 6.5mm	ZHENBIN
	△	2018.12.03	Modify the drawing frame and add the critical dimension	ZHENBIN
	△	2018.12.03	Add the reference dimension and note description	ZHENBIN
	△	2018.12.03	Update the RoHS compliant & add the body color.	ZHENBIN
	△	2018.12.03	Change the dimension from 1.0mm to 0.95mm	ZHENBIN
		2018.12.03	Change the dimension from 2.54mm to 3.14mm	ZHENBIN

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item① Terminal housing :Thermoplastic (UL 94V-0)
- Item② Clamp : Brass , Ni plated
- Item③ Wire guard solder pin , Brass , Tin plated
- Item④ Terminal screw: Steel Zinc plating'+/-"slot type

Electrical cULus

- Voltage rating: 300V
- Current rating: 10A
- Torque(Lb-In): 3.5
- Screw: M3.0
- Wrie range:
- SOLID WIRE(AWG): 16-26
- Stranded wire(AWG): 16-26
- Wire strip length: 6~7mm
- Withstanding Voltage:1.6KV
- Operating temperature: -40°C to +115°C
- Wave Soldering reliability: 260°C±5°C/5 Sec

- △ Safety Approval: cULus
- △ Critical dimension:
- △ Reference dimension: (×)The dimensions of pitch are just for

reference, take the actual assembly result as a judgment when inserting the terminal block into the PCB hole.

YS xx 2 0 x 0 xxxx G

△ RoHS compliant (Lead<4% In copper Alloy)

No. of poles end stackable design
04 2x2P POLES
06 2x3P POLES
...
48 2x24P POLES

0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)
C Green(RAL6018/U)
0000:"@ "Logo (Standard)
000A:"ANYTEK"Logo
Any special item by customer request, please contact sales department.

Amphenol
ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		YS-5.08 Series 2x2P-2x24P (Stackable)			
PART NO.	YSxx20x0xxxxG			DWG NO.	8YS0005
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		ZHENBING 2018.12.03	ZHENBING 2018.12.03		Tolerance
					X. ±0.50
					X.X ±0.30
					X.XX ±0.10
					X° ±1°
SHEET: 01/01		REV.: E			