







ABcDEF

NOTES 1 LEAD CO-PLANARITY SHALL BE 0.08 mm MAX.
 2 IF THERE IS PATTERN ON  PART, THERE IS A POSSIBILITY THAT IT WILL MAKE CONTACT WITH THE LEADS.
 3 REINFORCED METAL FITTINGS AS FOLLOWS.
 4 CAV NO. ARE INDICATED IN APPROXIMAL POSITION SHOWN.



2	PHOSPHOR BRONZE	CONTACT AREA:GOLD PLATED 0.2μm min	5	POLYESTER	CLEAR (COVER TAPE)
		LEAD AREA:GOLD PLATED 0.015μm min	4	PS	CLEAR (EMBOSSSED CARRIER TAPE)
		OTHERS(UNDER PLATING):NICKEL PLATED 2μm min	3	BRASS	TIN PLATED 2μm min (UNDER PLATING):NICKEL 1μm min
1	POLYAMIDE	UL94V-0・NATURAL (BEIGE)			
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS

UNITS mm		SCALE 5 : 1		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
 HIROSE ELECTRIC CO.,LTD.	APPROVED	・WR. FUKUCHI	20190409	DRAWING NO.	EDC-163507-86-78			
	CHECKED	・WR. FUKUCHI	20190409	PART NO.	DF12(3.0)-*DP-0.5V(86)			
	DESIGNED	・KT. KUSAKA	20190409	CODE NO.	CL537			
	DRAWN	・RN. IIDA	20190409					

