







N=Number of poles

Dim L	$(N-1) \times 3.81 + 5.0$
Dim B	$(N-1) \times 3.81$
Dim D	$(N-1) \times 3.81$

Poles	Tolerance
2p-6p	± 0.15
7p-12p	± 0.20
13p-16p	± 0.30



SIGN	DATE	DESCRIPTION	APPROVER

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item ① Male contact pin: Copper, Bright Tin plated over Nickel plated
- Item ② Terminalhousing: LCP (UL94V-0)
- Item ③ With cover: LCP (UL94V-0)

Electrical:

- Voltage rating: 300V
- Current rating: 10A
- Withstanding Voltage: 1.6 KV
- Operating temperature: -45°C to +130°C
- Soldering temperature: 260°C/10 Sec max
- Safety Approval: cULus

OQ xx 3 G x 0 Bxxx G

No. OF POLES
02: 2 POLES
03: 3 POLES

16: 16 POLES

Color
0: Black (RAL9005)

G RoHS compliant
(lead<4%)
In copper Alloy

B000: "@" Logo (Standard)
B00A: "ANYTEK" Mark
Any special item by
customer request,
please contact sales
department.



Amphenol
ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD.

TITLE				OQ 3.81mm 180° Series 2P-16P Close THR (With cover & Tape reel)						
PART NO.				OQxx3Gx0B000G		DWG NO.		80Q0F17		
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance			
		CHENMING 2016.12.14	CHENMING 2016.12.14				UNIT: mm		X.	±0.50
							SCALE: NONE		X.X	±0.30
							REV: B		X.XX	±0.10
				SHEET: 01/01		X°				±1°