



| SYMBOL DEFINITION                                                                                                                              |                                        | MISSING SYMBOLS             |  |
|------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------|-----------------------------|--|
| A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL<br>□ DOES NOT REQUIRE INSPECTION. IT MAY BE<br>CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING. | TOTAL NO OF<br>INSPECTIONS<br>REQUIRED | NO MISSING SYMBOL<br>NUMBER |  |
|                                                                                                                                                | LAST NO.<br>USED                       |                             |  |
|                                                                                                                                                | 32                                     |                             |  |
|                                                                                                                                                | 32                                     |                             |  |


| DWS STATUS |     |     |     | REVISION HISTORY |      |                                                                                    |  | AUTH   |     | APVD/APV |     |
|------------|-----|-----|-----|------------------|------|------------------------------------------------------------------------------------|--|--------|-----|----------|-----|
| DATE       | STG | REV | N/P | CHG              | ZONE |                                                                                    |  |        |     |          |     |
| 16MR04     | R   | 06  | -   | -                | -    | ALL PARTS - WERE SEPARATE DWGS AND<br>UPDATED MAT'L SPEC                           |  | 252884 | JVM | JVM      | EJH |
| 16JL04     | R   | 07  | -   | -                | -    | ALL ACTIVE PARTS - UPDATED PDM<br>ATTRIBUTES                                       |  | 256676 | ESH | FRG      | DER |
| 26A004     | R   | 08  | -   | -                | -    | 12089238- OBSOLETE REPLACED BY 12103511                                            |  | 257914 | ADK | ADK      | GR  |
| 120C15     | R   | 09  | -   | -                | -    | 02984799, 02989716, 08917796, 12015106,<br>12015811, 12015812, 12015910 - OBSOLETE |  | 431008 | AHY | AHY      | ERG |




TYPE 201




TYPE 202



TYPE 203  
SAME AS TYPE 202  
EXCEPT AS SHOWN



TYPE 204  
SAME AS TYPE 201  
EXCEPT AS SHOWN



TYPE 205  
SAME AS TYPE 201  
EXCEPT AS SHOWN

NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:  
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND  
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION.  
(SEE MATH MODEL FOR PRECISE DIMENSIONS.) FOR ALL  
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL  
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.

|           |            |        |
|-----------|------------|--------|
| .533±.003 | 1/2        | ---    |
| .471±.003 | 7/16       | ---    |
| .407±.003 | 3/8        | M10    |
| .345±.003 | 5/16       | M8     |
| .282±.003 | 1/4        | M6.3   |
| .244±.003 | #12        | M6     |
| .235±.003 | #12        | M6     |
| .204±.003 | #10        | M5     |
| A DIA     | STANDARD   | METRIC |
|           | SCREW/STUD | SIZE   |

| PROCESS SENSITIVE DIMENSION                                                                            |         | THIRD ANGLE PROJECTION |    | DO NOT SCALE |  |
|--------------------------------------------------------------------------------------------------------|---------|------------------------|----|--------------|--|
| DIMENSIONS ENCLOSED IN ( ) INDICATE<br>REFERENCE DIMENSIONS AND NO TOLERANCE<br>LIMITS ARE ESTABLISHED | CHART J | USE MATH DATA          | NX |              |  |
| FROM 0 TO 500<br>TOLERANCE UNLESS OTHERWISE SPECIFIED<br>±.005 ±.010                                   | CHART J |                        |    |              |  |
| ANGULAR TOLERANCE 12°                                                                                  |         |                        |    |              |  |

|                                                                                                        |  |                                                                                                                                                                                                                                      |  |
|--------------------------------------------------------------------------------------------------------|--|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|
| A LINE DRAWN THROUGH A PART NUMBER<br>INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE<br>FOR ORDERING. |  | PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE<br>THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING.                                                                                                                             |  |
| CONTACT DELPHI SALES TO ASSURE AVAILABILITY<br>OF PARTS.                                               |  | THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994<br>AS MODIFIED BY THE 2003 GLOBAL DIMENSIONING AND<br>TOLERANCING ADDENDUM-2001. SEPARATE PATTERNING OF<br>FEATURES MAY BE OBTAINED SEPARATELY. RESIDUES OF DATA<br>REFERENCES. |  |
| DWG TYPE                                                                                               |  | PART DRAWING                                                                                                                                                                                                                         |  |
| STYLE                                                                                                  |  | D                                                                                                                                                                                                                                    |  |
| VOLUME (OMP)                                                                                           |  | DISTR CODE                                                                                                                                                                                                                           |  |
| UNLESS OTHERWISE SPECIFIED                                                                             |  | THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994<br>AS MODIFIED BY THE 2003 GLOBAL DIMENSIONING AND<br>TOLERANCING ADDENDUM-2001. SEPARATE PATTERNING OF<br>FEATURES MAY BE OBTAINED SEPARATELY. RESIDUES OF DATA<br>REFERENCES. |  |
| ALL DIMENSIONS ARE IN INCHES                                                                           |  | REFERENCE                                                                                                                                                                                                                            |  |
| THIRD ANGLE PROJECTION                                                                                 |  | DO NOT SCALE                                                                                                                                                                                                                         |  |
| USE MATH DATA                                                                                          |  | NX                                                                                                                                                                                                                                   |  |

| DELPHI               |  | DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE                                                                                                                                                                                                  |  |
|----------------------|--|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|
| WARREN, OH           |  | COPYRIGHT 2004 DELPHI CORPORATION AND/OR ITS AFFILIATES.                                                                                                                                                                                           |  |
| ALL RIGHTS RESERVED. |  | THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION<br>AND CONTAINS DELPHI CONFIDENTIAL INFORMATION.<br>THE REPRODUCTION, DISTRIBUTION AND UTILIZATION<br>OF THIS DOCUMENT OR ITS RELATED CAD DATA<br>WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED. |  |
| DATE                 |  | SUBSTANCES OF CONCERN AND RECYCLED<br>CONTENT, PER DELPHI 10449901                                                                                                                                                                                 |  |
| OR                   |  | DRAWING NUMBER                                                                                                                                                                                                                                     |  |
| APVD1 J. VILLAMIL    |  | TAXI TERM RING STR                                                                                                                                                                                                                                 |  |
| APVD2 J. VILLAMIL    |  | DRAWING NUMBER                                                                                                                                                                                                                                     |  |
| APVD3 E. HAROLDSON   |  | 02962869                                                                                                                                                                                                                                           |  |
| APVD4                |  | SIZE A0                                                                                                                                                                                                                                            |  |
| APVD5                |  | SCALE 5:1                                                                                                                                                                                                                                          |  |
|                      |  | FRAME NO 1 OF 1                                                                                                                                                                                                                                    |  |
|                      |  | SHEET NO 2 OF 2                                                                                                                                                                                                                                    |  |
|                      |  | STG REV N/P                                                                                                                                                                                                                                        |  |
|                      |  | R 09                                                                                                                                                                                                                                               |  |

|           |     |     |               |            |          |     |     |            |                       |                     |          |     |           |      |        |      |       |       |
|-----------|-----|-----|---------------|------------|----------|-----|-----|------------|-----------------------|---------------------|----------|-----|-----------|------|--------|------|-------|-------|
|           |     |     | .0403 X 1.250 |            | 12013908 | A   | 1   | M3649159   | 8.0                   | 5.54-5.28           | 8        | 205 | .282±.003 | .260 |        |      |       |       |
|           |     |     | .0320 X 1.250 |            | 12089562 | A   |     | M3649134   | (2) 1.0 - 0.8         | 2.70-1.90           | 217      | 205 | .345±.003 | .201 |        |      |       |       |
|           |     |     | .0320 X 1.250 |            | 12089238 | A   | 2   | M3649134   | (2) 1.0 - 0.8         | 2.70-1.90           | 217      | 205 | .282±.003 | .201 |        |      |       |       |
|           |     |     | .0320 X 1.250 |            | 12089237 | A   | 1   | M3649134   | 1.0 - 0.8             | 2.70-1.90           | 17       | 205 | .282±.003 | .142 |        |      |       |       |
|           |     |     | .0320 X 1.250 |            | 12084522 | A   | 1   | M3649134   | 3.0 - 2.0             | 3.70-2.50           | 13       | 205 | .407±.003 | .185 |        |      |       |       |
| 12048427  | B   | 1   |               | 02962953   | 12015810 | B   | 2   | M3649134   | 5.0 - 3.0             | 4.48-3.39           | 11       | 201 | .407±.003 | .240 | 60°    | .098 | .054  |       |
|           |     |     | .0320 X 1.250 |            | 12015910 | B   | 2   | M3649134   | 2.0 - 1.0 & 0.8 - 0.5 | 3.97 MAX & 3.13 MAX | 1519     | 204 | .407±.003 | .170 | -      | -    | -     |       |
|           |     |     | .0320 X 1.250 |            | 12015909 | B   | 1   | M3649134   | 2.0 - 1.0             | 3.97 MAX            | 15       | 204 | .407±.003 | .170 | -      | -    | -     |       |
|           |     |     | .0320 X 1.250 |            | 12015908 | B   | 1   | M3649134   | 2.0 - 1.0 & 0.8 - 0.5 | 3.97 MAX & 3.13 MAX | 1519     | 204 | .345±.003 | .240 | -      | -    | -     |       |
|           |     |     | .0320 X 1.250 |            | 12015907 | B   | 1   | M3649134   | 2.0 - 1.0             | 3.97 MAX            | 15       | 204 | .345±.003 | .170 | -      | -    | -     |       |
|           |     |     | .0320 X 1.172 |            | 12015812 | C   | 2   | M3649131   | (2) 0.8 - 0.5         | 3.13-2.69           | 219      | 203 | .407±.003 | .160 | -      | -    | -     |       |
|           |     |     | .0320 X 1.172 |            | 12015811 | C   | 2   | M3649131   | (2) 0.8 - 0.5         | 3.13-2.69           | 219      | 203 | .345±.003 | .160 | -      | -    | -     |       |
| 12015106  | C   | 2   | .0403 X 1.250 | M3614159   |          |     |     |            | 8.0                   | 5.54-5.28           | 8        | 201 | .244±.003 | .260 | -      | -    | -     |       |
| 12010836  | C   | 1   | .0403 X 1.250 | M3614159   |          |     |     |            | 8.0                   | 5.54-5.28           | 8        | 201 | .471±.005 | .260 | -      | -    | -     |       |
| 12010245  | C   | 1   | .0403 X 1.250 | M3614159   |          |     |     |            | 5.0 & 1.0             | 3.56-3.36           |          | 201 | .345±.003 | .280 | -      | -    | -     |       |
| 12004984  | C   | 1   | .0403 X 1.250 | M3614159   | 12010953 | C   |     | M3649159   | 8.0                   | 5.54-5.28           | 8        | 201 | .533±.005 | .260 | -      | -    | -     |       |
| 12004983  | C   | 1   | .0403 X 1.250 | M3614159   | 12010047 | C   |     | M3649159   | 5.0 - 3.0             | 4.48-3.49           | 11       | 201 | .533±.005 | .230 | -      | -    | -     |       |
| 12004483  | C   | 1   | .0403 X 1.250 | M3614159   |          |     |     |            | 2.0 - 1.0             | 3.97-3.36           | 15       | 201 | .533±.005 | .165 | -      | -    | -     |       |
| 12004370  | B   |     | .0403 X 1.250 | M3614159   |          |     |     |            | 8.0                   | 7.24-6.48           |          | 201 | .407±.003 | .260 | -      | -    | -     |       |
| 12004369  | B   |     | .0403 X 1.250 | M3614159   |          |     |     |            | 8.0                   | 7.24-6.48           |          | 201 | .345±.003 | .260 | -      | -    | -     |       |
| 12004368  | B   |     | .0403 X 1.250 | M3614159   |          |     |     |            | 8.0                   | 7.24-6.48           |          | 201 | .282±.003 | .260 | -      | -    | -     |       |
| 08911796  | C   | 2   | .0403 X 1.250 | M3614159   |          |     |     |            | 5.0 - 3.0             | 4.48-3.49           | 11       | 201 | .471±.005 | .230 | -      | -    | -     |       |
| 089117642 | C   | 1   | .0403 X 1.250 | M3614159   | 12016822 | C   |     | M3614159   | 8.0                   | 5.54-5.28           | 8        | 201 | .282±.003 | .260 | -      | -    | -     |       |
| 08911809  | E   |     | .0403 X 1.250 | M3614159   |          |     |     |            | 8.0                   | 5.54-5.28           | 8        | 201 | .235±.003 | .260 | -      | -    | -     |       |
| 08911351  | E   |     | .0403 X 1.250 | M3614159   |          |     |     |            | 5.0 & 1.0             | 3.56-3.36           |          | 201 | .204±.003 | .280 | -      | -    | -     |       |
| 06288377  | CK  |     | .0320 X 1.172 | M3614131   |          |     |     |            | 2.0 - 1.0             | 3.05-2.48           | 15       | 202 | .407±.003 | .160 | -      | -    | -     |       |
| 02969948  | CJ  |     | .0403 X 1.250 | M3614159   |          |     |     |            | 8.0                   | 5.54-5.28           |          | 201 | .407±.003 | .260 | -      | -    | -     |       |
| 02969716  | CK  | 2   | .0320 X 1.172 | M3614131   |          |     |     |            | (2) 0.8 - 0.5         | 3.13-2.69           | 219      | 202 | .345±.003 | .160 | -      | -    | -     |       |
| 02969606  | CK  | 1   | .0320 X 1.172 | M3614131   |          |     |     |            | 0.8 - 0.5             | 2.40-2.03           | 19       | 202 | .345±.003 | .140 | -      | -    | -     |       |
| 02964799  | CK  | 2   | .0403 X 1.250 | M3614159   |          |     |     |            | 2.0 - 1.0             | 3.97-3.36           | 15       | 201 | .471±.005 | .165 | -      | -    | -     |       |
| 02964756  | CK  | 1   | .0320 X 1.172 | M3614131   |          |     |     |            | 0.8 - 0.5             | 2.40-2.03           | 19       | 202 | .407±.003 | .140 | -      | -    | -     |       |
| 02964278  | CK  |     | .0403 X 1.250 | M3614159   |          |     |     |            | (1) 0.8 - (2) 5.0     | ----                |          | 201 | .407±.003 | .280 | -      | -    | -     |       |
| 02977493  | BK  | 1   | .0403 X 1.250 | M3614159   | 12016821 | BK  |     | M3649159   | 2.0 - 1.0             | 3.97-3.36           | 15       | 201 | .407±.003 | .165 | -      | -    | -     |       |
| 02977492  | BK  | 1   | .0403 X 1.250 | M3614159   | 05254088 | BK  |     | M3649159   | 2.0 - 1.0             | 3.97-3.36           | 15       | 201 | .345±.003 | .165 | -      | -    | -     |       |
| 02977491  | BK  | 1   | .0403 X 1.250 | M3614159   | 05254089 | C   |     | M3649159   | 8.0                   | 5.54-5.28           | 8        | 201 | .345±.003 | .260 | -      | -    | -     |       |
| 02977490  | BK  | 1   | .0403 X 1.250 | M3614159   | 02969936 | BK  |     | M3649159   | 5.0 - 3.0             | 4.48-3.49           | 11       | 201 | .345±.003 | .230 | -      | -    | -     |       |
| 02962976  | BK  | 1   | .0403 X 1.250 | M3614159   | 12016823 | BL  |     | M3649159   | 8.0                   | 5.54-5.28           | 8        | 201 | .407±.003 | .260 | -      | -    | -     |       |
| 02962953  | BK  | 1   | .0403 X 1.250 | M3614159   | 02977444 | BK  |     | M3649159   | 5.0 - 3.0             | 4.48-3.49           | 11       | 201 | .407±.003 | .230 | -      | -    | -     |       |
| PART NO   | REV | N/P | MAT'L SIZE    | MAT'L SPEC | PART NO  | REV | N/P | MAT'L SPEC | SIZE (MMF)            | CABLE               | DIA (MM) | ID  | TYPE      | A    | G±.015 | V±5° | W±.03 | X±.03 |
|           |     |     | UNPLATED      |            |          |     |     | PLATED     |                       |                     |          |     |           |      |        |      |       |       |