



SYMBOL DEFINITION		MISSING SYMBOLS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL ○ DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	NO MISSING SYMBOL NUMBER	
	LAST NO. USED		
	8		
	8		



CWS STATUS		REVISION HISTORY		AUTH		DR		APVD/APVD	
DATE	STG	REV	N/P	CHG	ZONE				
11JUL01	R	01	-	-		ALL ACTIVE PARTS - REVISED GRAPHICS		211315	RVP/RVP JH
17JUL03	R	02	-	-		I2020156 - PER ECN 211315 REV LEVEL L2 SHOULD BE K1, CORRECT REV LEVEL TO K2		243603	JYD/JYD JH
01AUG06	R	03	-	-		I2020156, I2033997 & I2066614 - MAT'L SPEC WAS P1519030		283052	MDH/JAA MKM
18FEB15	R	04	-	-		I2176854 - ADDED TARNISH INFO NOTE		428877	ABH/JVM JSM
02SEP16	R	05	-	-		ALL ACTIVE PARTS - UPDATED GRAPHICS TO "PXX" INSTEAD OF "PED"		434044	JVM/JVM LES
24AUG17	R	06	-	-		I2176854 - UPDATED PDM ATTRIBUTES		437588	ABH/ABH LB



TYPE 102
SAME AS TYPE 101
EXCEPT AS SHOWN



TYPE 103
SAME AS TYPE 101
EXCEPT AS SHOWN



TYPE 101

NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:

DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.

2. RECOMMENDED MATING BLADES - (1) METRI-PACK (0.86/0.79 THK. X 6.38/6.22 WIDE)
(2) AUTOFUSE (0.69/0.61 THK X 5.355/5.11 WIDE)

3. THIS PART FOR DIAGNOSTIC INDUSTRY APPLICATIONS.

4. DO NOT PROBE, TEST OR OTHERWISE CONTACT THE INTERIOR REGION (THE SPRING OR ANY MOVING PART) OF THIS TERMINAL. SEVERE DAMAGE CAN OCCUR, COMPROMISING THE PERFORMANCE OF THE ELECTRICAL INTERFACE.

5. FOR TERMINALS PACKAGED & STORED IN THE APPROVED MANNER, TARNISH ON SILVER PLATED SURFACES WILL NOT AFFECT THE PERFORMANCE OF THE PART.

PART NO	REV	N/P	MAT'L SIZE	MAT'L SPEC	PART NO	REV	N/P	MAT'L SIZE	MAT'L SPEC
12066506	A	-	0.406 X 35.71	COPPER ALLOY	12176854	A5	-	0.406 X 35.71	AG PLATED COPPER ALLOY
12066505	B	-	0.406 X 35.71	COPPER ALLOY	12020156	K4	-	0.406 X 35.71	TIN PLATED COPPER ALLOY
12066504	B	-	0.406 X 35.71	COPPER ALLOY	12066614	A3	-	0.406 X 35.71	TIN PLATED COPPER ALLOY
					12033997	E4	-	0.406 X 35.71	TIN PLATED COPPER ALLOY
					12020157	H	-	0.406 X 35.71	TIN PLATED COPPER ALLOY
UNPLATED					PLATED				
PART NO	REV	N/P	MAT'L SIZE	MAT'L SPEC	PART NO	REV	N/P	MAT'L SIZE	MAT'L SPEC

PROCESS SENSITIVE DIMENSION	
4	
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED	
DIMENSIONAL RANGE (MM)	CHART ID
FROM 0 TO 12	> 12
TOLERANCE UNLESS OTHERWISE SPECIFIED	
±0.1	±0.2
ANGULAR TOLERANCE	±2°

THIRD ANGLE PROJECTION	
DO NOT SCALE	USE MATH DATA

DELPHI	
DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE	
WARREN, OH	
COPYRIGHT 1988 DELPHI CORPORATION AND/OR ITS AFFILIATES. ALL RIGHTS RESERVED.	
THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION AND CONTAINS DELPHI CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD DATA, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.	
DATE	
DR	
APVD1 J. KRAUSE	15MR88
APVD2 D. STEELE	14AP88
APVD3 G. SMALDINO	21AP88
APVD4	
APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT, PER DELPHI (9244990)	
MATERIAL SEE CHRT	
DRAWING NAME	
TAXI TERM F M/P 630	
DRAWING NUMBER	
12020155	
SIZE A0	SCALE 8:1
FRAME NO 1 OF 1	SHEET NO 1 OF 3
STG R	REV 06