

simpleRTK3B Micro

affordable and low power dual/triple band GPS/GNSS RTK boards that allow you to reach millimeter-level accuracy in minutes, based on Septentrio Mosaic.



SKU: AS-RTK3B-MICRO-MX

Dimensions: 38x32x11mm

Key features

- Millimeter level precision
 - <1cm with a base station up to 35km
 - <1cm with NTRIP up to 35km
 - <1.2m in standalone mode
 - <0.6m standalone with SBAS coverage
- Based on Septentrio Mosaic-X5
- Update rate
 - Default: 1Hz
 - With maximum performance: up to 100Hz
- Multi band: L1, L2 and L5 support, 448 hardware channels
- Protocols:
 - Septentrio Binary Format (SBF)
 - NMEA 0183, v2.3, v3.03, v4.0
 - RINEX v2.x, v3.x
 - RTCM v2.x, v3.x (MSM included)
 - CMR v2.0 (out/in), CMR+ (input only)
- Start-up times:
 - Cold start: <45s
 - Warm start: <20s
 - Re-acquisition: 1s

Mechanical

- Weight 9 gr

Electrical

- Interfaces (check product documentation to verify which are available):
 - USB, UART, Timepulse, Event, Ethernet
- Base and Rover functionality
- Operating temperature Range: -40 to +85deg

Environmental

- Certification: CE, WEEE, ISO 9001-2015
- Documentation: RED, RoHS

Supported frequencies

- GPS: L1C/A L1PY L2C L2P L5
- GLONASS: L1CA L2CA L2P L3 CDMA
- BeiDou: B1I B1C B2a B2I B3
- Galileo: E1 E5a E5b E5 AltBloc E6
- QZSS: L1C/A L2C L5
- Navic: L5
- SBAS: WAAS, EGNOS, MSAS, GAGAN, SDCM (L1 L5)