







SYMBOL DEFINITION		MISSING NUMBERS	
THE NUMBER INSIDE THE SYMBOL CORRESPONDS TO THE NUMBER ON THE INSPECTION REPORT FOR THIS DRAWING/PART NUMBER	TOTAL NO. OF SYMBOLS ON DRAWING	19	
	LAST NO. USED	21	

DWG STATUS					REVISION HISTORY					AUTH		DR	APVD	APVD
DATE	STG	REV	N/P	CHG	ZONE									
15AP03	R	D6	-	-		CLEARED REV COLUMN, ADDED DELPHI LOGO NOTE & RECYCLING CODE NOTE AND REVISED				239787	RH	RH	AM	
19MY03	R	D7	-	-		ADDED LABEL				241328	KGP	KGP	ET	
23FE04	R	D8	-	-		UPDATED PDM ATTRIBUTES				252209	EES	EES	SN	
28NO18	R	D9	-	-		UPDATED DESIGN & ENGINEERING CONTROL AND ADDED NOTE				441674	JLL	JAA	RJR	

THE DESIGN AND ENGINEERING CONTROL OF THIS COMPONENT HAS BEEN TRANSFERRED TO APTIV/HELLERMANNTYTON



EJECTOR PADS OPTIONAL AND PERMISSIBLE, LOCATED APPROXIMATELY AS SHOWN.



PREFERRED OPTIONAL CONSTRUCTION
SCALE 2:1

- NOTES
- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
 - MATERIAL RECYCLING CODE PER ISO 11469, (0.1)X(0.01) CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE.
 - CORPORATE BRAND TO BE APPLIED TO PRODUCT DESIGN PER THE LATEST REVISION OF ESD S1085201.
 - THIS PART TO FIT .750 I.D. CONVOLUTED CONDUIT.
 - RECOMMENDED HOLE SIZE FOR CLIP .240-.260 DIA HOLE IN .150 MAX THICK STOCK.

PROCESS SENSITIVE DIMENSION				
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED				
DIMENSIONAL RANGE (IN)	CHART		H	
FROM	0	>.750	>1.250	>2.750
TO	.750	1.250	2.750	4.000
TOLERANCE UNLESS OTHERWISE SPECIFIED				
	±.005	±.010	±.012	±.016
				±.020
ANGULAR TOLERANCE ±2°				
4				