



This drawing is the property of Tusonix, Inc., and may not be used, reproduced, published or disclosed to others without expressed authorization by Tusonix Inc.

DATA SHEET DRAWING

Electrical testing per Tusonix standard test plans and MIL-Std-202 test methods.



B	Cx (pF)	TOL.	DC WORKING VOLTAGE		I DC	I.R. MIN @ 100 VDC	DWV	DIMENSIONS: ENGLISH UNITS - INCHES METRIC UNITS - [mm]	TUSONIX A Subsidiary of CTS, Electronic Components TUCSON, ARIZONA --TOLERANCES-- Unless Otherwise Specified	Title				
	1000	+100% -0%	85°C 150	125°C 100	1A	10 G Ω	250 VDC			MINIATURE PRESS-IN EMI FILTER				
	TYPICAL NO LOAD INSERTION LOSS (dB) @ 25°C PER MIL-STD-220							ORIENTATION 		Dwn	R.C. 12-02-15	Ckd	R.C. 12-02-15	
	10 MHz		100 MHz		1 GHz		10 GHz			Material	SEE NOTES		Scale:	NOT TO SCALE
	5		20		35		45					Sheet 1 of 1		
A	REVISION RECORD							2 Place Decimal ±	.01	A	4310-017			
	REV	DATE	CHG BY	CHANGE	REV	DATE	CHG BY	CHANGE	3 Place Decimal ±				.005	
	A	12-02-15	R.C.	ORIGINAL RELEASE					Angles ±				5 °	
	B	09-29-16	R.C.	MODIFIED DOT PLACEMENT, NOTE 5 HOLE DIM., ADDED EPOXY FILL NOTE.										