



NOTA NOTE	SPECIFICATIONS
1	CONNECTEUR DOIT ETRE CONFORME AU CDC: FEMALE CONNECTOR ACCORDING TO PSA SPECIFICATION: 96 238 404 99
2	CONNECTEUR SUIVANT: FEMALE CONNECTOR ACCORDING TO: -CLASSE DE TEMPERATURE T3 SELON B217050 REV A -TEMPERATURE CLASS T3 ACCORDING TO B217050 REV A -CLASSE DE VIBRATION MOTEUR SELON B217050 REV A -ENGINE VIBRATOR CLASS ACCORDING TO B217050 REV A -CLASSE ETANCHEITE 2 SELON B217050 REV A -SEALING CLASS 2 ACCORDING TO B217050 REV A
3	PRECONISATION D'UTILISATION: USER'S MANUAL : PU 071
4	ALVEOLE SUIVANT: CAVITY ACCORDING TO STE: 96 288 230 99
5	CONNECTEUR ET POSITION ALVEOLE CONFORMES AU PLAN D'INTERFACE: FEMALE CONNECTOR AND CAVITY'S POSITION ACCORDING TO: 211FT0289 ET/AND STE 96 339 622 99
6	CONDUCTEUR SUIVANT / WIRE ACCORDING TO: STE : 96 418 794 99
7	CONDITIONNEMENT SUIVANT NORME: PACKAGING ACCORDING TO STANDARD: E73 03 1506
8	DIAMETRE DE FILS / WIRE DIAMETER Ø 1.5 MINI=1.40 MAXI=2.80 Ø 2.8 MINI=1.60 MAXI=3.45
9	MASSE DU PRODUIT LIVRABLE / DELIVERY CONNECTOR WEIGHT: 12g
10	CHARNIERE DE PLAQUETTE ARRIERE ABSENTE OU CASSEE ADMISE NO WAFER HINGE OR WAFER HINGE BROKEN ALLOWED
11	DEFAUTS D'ASPECT SUR ZONES NON FONCTIONNELLES ADMIS VISUAL DEFECTS ON NO FUNCTIONNAL AREAS ALLOWED



PORTE-CLIPS 6V 1.5 FEMALE HOUSING 6V 1.5	PORTE-CLIPS FEMALE HOUSING	211 I 8 077	33501298	PBT 0% FV PBT 0% GF	GRIS GREY
	GRILLE GRID	211 M 1 125	33501311	PBT 15% FV PBT 15% GF	MARRON BROWN
		211 M 4 125	15537747		JAUNE YELLOW
		211 M 5 125	33508061		VERT GREEN
	GRONMET GROMMET	211 M 137	33501312	SILICONE 30Sh SILICON 30Sh	BLEU BLUE
PORTE-CLIPS 6V MIXTE FEMALE HOUSING 6V MIXED	JOINT INTERFACIAL INTERFACE SEAL	211 M 077	33501306	SILICONE 30Sh SILICON 30Sh	BLEU BLUE
	PORTE-CLIPS FEMALE HOUSING	211 I 0 075	33501295	PBT 0% FV PBT 0% GF	NOIR BLACK
	GRILLE GRID	211 M 0 123	33501301	PBT 15% FV PBT 15% GF	NOIR BLACK
		211 M 6 123	33508062		BLEU BLUE
		211 M 8 123	33501317		GRIS GREY
	GRONMET GROMMET	211 M 110	33501310	SILICONE 30Sh SILICON 30Sh	VERT GREEN
	JOINT INTERFACIAL INTERFACE SEAL	211 M 077	33501306	SILICONE 30Sh SILICON 30Sh	BLEU BLUE
	DESIGNATION DESCRIPTION	REF. ORIGINE LEBAC'S REFERENCE	REF. ORIGINE DELPHI'S REFERENCE	MATIERE MATERIAL	COULEUR COLOUR



PORTE-CLIPS 6V MIXTE 6 WAY MIXED FEMALE HOUSING			PORTE-CLIPS 6V 1.5 6 WAY 1.5 FEMALE HOUSING			VUE F VIEW F ±0.10	
						COULEUR COLOUR	
NOIR BLACK	BLEU BLUE	GRIS GREY	MARRON BROWN	JAUNE YELLOW	VERT GREEN		
211 PC 06 95 0 149	211 PC 06 95 6 149	211 PC 06 9 5 8 149	211 PC 06 2 5 1 149	211 PC 06 2 5 4 149	211 PC 06 2 5 5 149	PART NUMBER	MVL
A	A	A	A	A	A	PART REVISION	
10866611	10866612	10866614	10865112	10866616	10866615	PART NUMBER	DELPHI
01	01	01	01	01	01	PART REVISION	

3D VIEW

ECHELLE 1:1
SCALE 1:1
CODAGE NOIR REPRESENTE
BLACK CODING REPRESENTED

LA LIGNE TRACÉE SUR LA RÉFÉRENCE
PIÈCE INDIQUE QUE LA PIÈCE N'EST PAS
DISPONIBLE À LA COMMANDE.

LES RÉFÉRENCES PIÈCES QUI NE SONT PAS BARRÉES
INDIQUENT QUE CELLES-CI SONT DISPONIBLES
PHYSIQUEMENT POUR ÊTRE COMMANDEES.

CONTACTER LE SERVICE COMMERCIAL DE DELPHI
POUR S'ASSURER DE LA DISPONIBILITÉ DES PIÈCES

R 0.2 MAX

SHARP CORNER TOLERANCE

Ø DIM TO CHECK
COTES À VÉRIFIER
() DIM FOR HELP
COTES POUR INFO
□ THEORETIC DIM
COTES THÉORIQUES

DO NOT
SCALE

USE MATH
DATA

DWG STATUS

DATE	STG	REV	N	P	CHG	ZONE	REVISION HISTORY	AUTH	DR	APVD 1	APVD 2
24JA15	R	01					FILE TRANSLATED FROM MVL SYSTEM		DGL	DGL	DGL
18JA18	R	01	AA			CE10 E5	REDRAWN IN NX DELPHI P/N ADDED DIMENSION WAS 13.80 ± 0.25		A.RAJ	S.THO	O.GOL

DWG TYP
CUSTOMER PART DRAWING

WEIGHT (GR)
SEE NOTE 9

VOLUME (CM³)

ROUTING

DISTR CODE
D

UNLESS OTHERWISE SPECIFIED

GENERAL TOLERANCES
ACCORDING TO:
±0.1 ±2°

GD&T
ACCORDING TO:

REFERENCE
211FT0515

FIRST ANGLE PROJECTION

DO NOT
SCALE

USE MATH
DATA

DELPHI

DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE
Chennai, India

COPYRIGHT 2018 DELPHI CORPORATION AND/OR ITS AFFILIATES.
ALL RIGHTS RESERVED.

THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION
AND CONTAINS DELPHI CONFIDENTIAL INFORMATION.
THE REPRODUCTION, DISTRIBUTION AND UTILIZATION
OF THIS DOCUMENT OR ITS RELATED CAD DATA,
AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS,
WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.

CE PLAN EST LE PROPRIÉTÉ DE DELPHI CORPORATION ET CONTIENT DES
INFORMATIONS DELPHI CONFIDENTIELLES. LA REPRODUCTION, LA DISTRIBUTION
ET L'UTILISATION DE CE DOCUMENT OU DE SES DONNÉES MATHÉMATIQUES CAD,
AINSI QUE LA COMMUNICATION DE TOUT CONTENU À AUTRUI, SANS AUTORISATION
EXPRESSE EST INTERDITE.

DR	DE MATOS	DATE
APVD1	S LACOTE	31OC03
APVD2	Pascal MENARD	19MA13
APVD3		
APVD4		
APVD5		

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001
MATIÈRES PRÉOCCUPÉES ET CONTENU RÉCYCLABLE SELON
DELPHI 10949001

MATERIAL
SEE TABLE

DRAWING NAME
6-WAY HYBRID FEMALE CONNECTOR

MINI SEALED "NM" FEMALE CONNECTOR

DRAWING NUMBER
10858268

SIZE	SCALE	FRAME NO	SHEET NO	STG	REV	N/P
A1	2:1	1 OF 1	1 OF 1	R	01	AA