





3					2		1		
DWS STATUS		ZONE			REVISION HISTORY		AUTH	RPVD	APVD
DATE	STG	REV	W/	CHG					
13AUG02	R	02	-	-	CLEARED REV COL: ALL PARTS - ADDED MAT'L SAVERS TO OPTIONAL CONSTRUCTION		229088	EOV	EOV FR
03EOC02	R	03	-	-	ALL PARTS - REVISED GRAPHICS		229993	RVP	RVP FR
28B0C02	R	04	-	-	ALL PARTS - REVISED GRAPHICS		323643	RVP	RVP FR
09NOV01	R	05	-	-	ALL PARTS - UPDATED DESIGN & ENGINEERING CONTROL AND ADDED NOTE		441375	LVD	JAA R



NOTES

- | | |
|---|------------|
| <p>1. LINE DRAWING THROUGH A PART NUMBER INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE FOR ORDERING.</p> <p>PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING.</p> <p>CONTACT MPTV SALES TO ASSURE AVAILABILITY OF PARTS.</p> | |
| <p>DWG TYPE: PART DRAWING</p> | |
| <p>STYLE: SEE CHART</p> | |
| VOLUME (CM ³) | DISTR CODE |
| SEE CHART | D |
| <p>UNLESS OTHERWISE SPECIFIED</p> <p>THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994
 TOLERANCING SYSTEM FOR GEOMETRIC DIMENSIONS AND TOLERANCES
 TO COORDINATE WITH ISO 1101-1992. ALL GEOMETRIC TOLERANCES
 ARE SPECIFIED USING THE MAXIMUM MATERIAL CONDITION (MMC)
 DOES NOT APPLY UNLESS RELATIONSHIP BETWEEN FEATURES
 IS SPECIFIED. UNLESS OTHERWISE SPECIFIED, UNLESS OTHERWISE
 SPECIFIED, POSITION CALLOUTS MAY BE GAGED SEPARATELY.
 ALL DIMENSIONS ARE TO BE REPRESENTED IN MILLIMETERS
 UNLESS OTHERWISE SPECIFIED.</p> | |
| <p>REFERENCE:</p> | |



DIMENSIONAL RANGE (MM)		CHART E								
FROM	TO	> 0 20	> 20 30	> 30 70	> 70 100	> 100 150	> 150 200	> 200 250	> 250 300	> 300 400
TOLERANCE UNLESS OTHERWISE SPECIFIED										
		±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.2
ANGULAR TOLERANCE ±2°										

