




SYMBOL DEFINITION		
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	11
	LAST NO. USED	8

DWG STATUS					ZONE	REVISION HISTORY		AUTH	DR	APVD1	APVD2
DATE	STG	REV	N/P	CHG							
17SE01	R	005	-	-	-	CLEARED REVISION COL. AND MAT'L SPEC WAS R0067547 PA6 BLK REDRAWN TO PD		214384	P-G	P-G	ET
04SE08	R	05	AA	-	-	ADDED BOW NOTE TO DIM #5 & APPEARANCE ITEM NOTE AND REVISED MAT'L CALLOUT TO GENERIC CALLOUT		406009	ECB	AUG	TP
09N018	R	05	AB	-	-	UPDATED DESING & ENGINEERING CONTROL AND ADDED NOTE		441375	LVD	JAA	RJR



THE DESIGN AND ENGINEERING CONTROL OF THIS COMPONENT HAS BEEN TRANSFERRED TO APTIV/HELLERMANN+TYTON



OPTIONAL CONSTRUCTION



OPTIONAL CONSTRUCTION



- NOTES
- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
 - THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM. MINOR IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR BLEMISHES, GATE VESTIGE, AND SOFT FLASH THAT DO NOT AFFECT THE FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER NAP 4.10-18.
 - THIS PART TO ACCEPT 30MM CONDUIT.
 - RECOMMENDED HOLE SIZE FOR CLIP 6.1-6.6 DIA. HOLE IN 3.81 MAX. THICK STOCK.
 - ANTI-RATTLE FEATURES ARE IDENTICAL
 - DIMENSIONS MARKED WITH ● MAY VARY -0.6 DUE TO BOW.

7. CORPORATE BRAND TO BE APPLIED TO PRODUCT DESIGN PER THE LATEST REVISION OF ESD 51085201.

DIMENSIONAL RANGE (MM)		CHART	
FROM	TO		ET
> 0	> 20	> 30	> 70
> 20	> 30	> 70	> 100
> 30	> 70	> 100	> 150
> 70	> 100	> 150	> 200
> 100	> 150	> 200	> 250
> 150	> 200	> 250	> 300
> 200	> 250	> 300	> 400
TOLERANCE (PLESS OTHERWISE SPECIFIED)			
±0.15	±0.2	±0.3	±0.4
±0.4	±0.5	±0.6	±0.8
±1	±1.2	±1.5	±2
ANGULAR TOLERANCE ±2°			

A LINE DRAWN THROUGH A PART NUMBER INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE FOR ORDERING.	
PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING.	
CONTACT APTIV SALES TO ASSURE AVAILABILITY OF PARTS.	
DWG TYPE	
PART DRAWING	
STYLE	DATE
VOLUME (GMT)	DISTR CODE
4.247	D
UNLESS OTHERWISE SPECIFIED	
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS MODIFIED BY THE GM GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM - 1997. ALL GEOMETRIC TOLERANCES AND RELATED DATUMS APPLY HERE. RULE #1 RESPECT FORM AT ALL TIMES. DIMENSIONS ARE TO UNLESS OTHERWISE SPECIFIED. SEPARATE POSITION CALLOUTS MAY BE USED SEPARATELY. ALL DIMENSIONS ARE IN MILLIMETERS.	
THIRD ANGLE PROJECTION	DO NOT SCALE
USE MATH DATA	NX
REFERENCE	
DRAWING NAME	
MOUN CLIP CDT 30MM ROSEBUD	
DRAWING NUMBER	
12048089	
SIZE	SCALE
A0	4:1
FRAME NO	SHEET NO
1 OF 1	1 OF 1
STG	REV
05	AB