



SYMBOL DEFINITION			MISSING NUMBERS
THE NUMBER INSIDE THE SYMBOL  CORRESPONDS TO THE NUMBER ON THE INSPECTION REPORT FOR THIS DRAWING/PART NUMBER	TOTAL NO. OF SYMBOLS ON DRAWING	7	
	LAST NO. USED	10	

DWG STATUS	ZONE	REVISION HISTORY				AUTH	DR	CK	APVD	
DATE	STG	REV	CHG	N/P						
06SE00	R	001	-	-		REDRAWN TO PD	000009	ECB	FRG	ET
15AU01	R	002	-	-		ADDED CHRYSLER REFERENCE NOTE	213158	HAM	HAM	ET
21N001	R	003	-	-		ALL PARTS - REVISED TOLERANCE CHART & FORMAT TO ENGLISH	217445	EES	EES	ET



NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
2. CLIP TO SNAP INTO .230 - .270 Ø HOLE IN .035 - .090 THICK STOCK.
3. ENVIRONMENTAL PROTECTION ACCORDING TO OPEL SPECIFICATION QU000001 - CADMIUM.
4. FOR PN-06288590 REFERENCE CHRYSLER PN-J4175366

DELPHI Automotive Systems			
MATERIAL SPEC SEE CHART			
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI-A 10949001			
PART DRAWING			DISTR CODE D
CODE NUMBER 6900	DWG DATE 27JA66	SCALE 2:1	
QC SPEC	STYLE	VOLUME in ³ 0.976	
PART GEOMETRY 3D SOLID	UNLESS OTHERWISE SPECIFIED: THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M - 1994 AS AMENDED BY THE GM GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM - 1997. ALL GEOMETRIC TOLERANCES AND RELATED DATUMS APPLY RFS. RULE #1 (PERFECT FORM AT MMC) DOES NOT APPLY WHEN RELATIONSHIP BETWEEN FEATURES IS ESTABLISHED BY ORIENTATION OR LOCATION TOLERANCES. SEPARATE POSITION CALLOUTS MAY BE GAGED SEPARATELY REGARDLESS OF DATUM REFERENCES.		
 CHANGE RESTRICTED NO MANUAL CHANGES	REFERENCE	DR	DATE
COPY OF MATH DATA DO NOT SCALE		APVD1 E.A. CACHO	06SE00
		APVD2 FCO. RESENDIZ	12SE00
		APVD3 ERIC TRACEY	13SE00
		APVD4	
		APVD5	
ENGLISH UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE IN INCHES	DRAWING NAME TAXI CLIP HARN		
THIRD ANGLE PROJECTION 			
SHEET NUMBER 1 OF 1	DRAWING NUMBER 12124254		DWG STATUS STG REV N/P R 003 -
			SIZE A2

DIMENSIONAL RANGE (IN) CHART H					
FROM	0	>.750	>1.250	>2.750	>4.000
TO	.750	1.250	2.750	4.000	
TOLERANCE UNLESS OTHERWISE SPECIFIED					
	±.005	±.010	±.012	±.016	±.020
ANGULAR TOLERANCE ± 2°					

12124253	R	A2	-		R0071769 PA66 HS IM-GRA LT
06288590	R	B3	-		R0071754 PA66 HS IM-BLK
PART NO	STG	REV	N/P	STATUS	MATERIAL SPECIFICATION AND COLOR