





SYMBOL DEFINITION		
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL  DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	7
	LAST NO. USED	6

MISSING SYMBOLS					DWG STATUS		ZONE	REVISION HISTORY	AUTH	DR	APVD	APVC				
NO MISSING SYMBOL NUMBER					DATE	STG							REV	N/P	CHG	
					27SE00	R	B1	-	-	CLEARED REV COLUMN & REDRAWN TO PD			227338	FM0/	GG1	
					27SE00	R	B2	-	-	UPDATED PDM ATTRIBUTES			202328	FM0/	GG1	
					08AP21	R	B3	-	-	UPDATED FORMAT TO LATEST STANDARDS AND REVISED OVERALL INSPECTION SYMBOLS			553978	GLG/	GLG	VRG



NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:

- DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM. MINOR IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR BLEMISHES, GATE VESTIGE, AND SOFT FLASH THAT DO NOT AFFECT THE FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER EAMP-4-3-CS-01-EN.
- CORPORATE BRAND TO BE APPLIED TO PRODUCT DESIGN PER THE LATEST REVISION OF ESD S1085201.
- FOR APPLICATION DATA SEE THE APPLICATION DRAWING.
- MAXIMUM CABLE DIAMETER FOR THIS PART IS 2.8 MM.

DIMENSIONAL RANGE (MM)		TOLERANCE (UNLESS OTHERWISE SPECIFIED)		CHART		TOLERANCE (UNLESS OTHERWISE SPECIFIED)		CHART	
FROM	TO								
> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300	> 400
±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.2	±1.6
ANGULAR TOLERANCE: ±2°									

A				B			
INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE FOR ORDERING.				INDICATES THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING.			
PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING.				CONTACT APTIV SALES TO ASSURE AVAILABILITY OF PARTS.			
DWG TYPE				PART DRAWING			
STYLE				3.521			
VOLUME (CM)				D			
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5-2019. SEE APTIV ENGINEERING DESIGN STANDARD 06-2017 FOR ISO 1101:2004 RECONCILIATION REQUIREMENTS.				ALL DIMENSIONS ARE IN MILLIMETERS			
REFERENCE				THIRD ANGLE PROJECTION			
DO NOT SCALE				USE MATH DATA			

A				B			
INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE FOR ORDERING.				INDICATES THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING.			
PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING.				CONTACT APTIV SALES TO ASSURE AVAILABILITY OF PARTS.			
DWG TYPE				PART DRAWING			
STYLE				3.521			
VOLUME (CM)				D			
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5-2019. SEE APTIV ENGINEERING DESIGN STANDARD 06-2017 FOR ISO 1101:2004 RECONCILIATION REQUIREMENTS.				ALL DIMENSIONS ARE IN MILLIMETERS			
REFERENCE				THIRD ANGLE PROJECTION			
DO NOT SCALE				USE MATH DATA			