









MISSING SYMBOLS	
	16

DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	APPROVAL	
DATE	STG	REV	N/P	CHG					1	2
260C15	R	01	-	-	ALL PARTS - RELEASED PART DRAWING	430764	SM	SM	SSS	
23N015	R	02	-	-	REVISED GRAPHICS	431467	SM	SM	SSS	
16MR16	R	03	-	-	REMOVED DIM #16 & BASIC DIM 2X 5.4B TYP	432094	KV	KV	SSS	
09JL16	R	04	-	-	SEPARATED FEATURE CONTROL FRAME ON DIMS #32 & #35, REVISED INTERCHANGEABLE TOOL NOTE & TOL 5 ON DIM #117 (PLCS) AND ADDED EVECTOR PIN NOTES	432604	SM	SM	SSS	
18JL16	R	05	-	-	REVISED DIM (7 PLCS) & DIM TOL (10 PLCS)	433596	SM	SM	SSS	
060C16	R	06	-	-	ADDED NOTES	434474	KA	KA	DDJ	
03N016	R	07	-	-	REVISED GRAPHICS	434721	SM	SM	DDJ	
07D16	R	08	-	-	ADDED OPTIONAL CONSTRUCTION VIEW AND REVISED PART AVAILABILITY	435082	SM	SM	DDJ	
04JA17	R	09	-	-	33267786 - CORRECTED PART NUMBER LABEL	435286	MSD	MSD	DDJ	
12JA17	R	10	-	-	DIM #10 WAS 3.1 +/- 0.1 & DIM #9 WAS 6.9	435357	NKS	NKS	DDJ	
06JL17	R	11	-	-	DIM #23 WAS 2X 27.5 +/-0.1 & BASIC DIM 2X 15.9 WAS 2X 16.1	437154	SM	SM	DDJ	



33267786
9MM CONDUIT

NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA
2. MATERIAL RECYCLING CODE PER ISO 11469, (1.5)X(1) CHARACTERS PA 66 LOCATED ON ANY EXTERIOR SURFACE
3. THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM, MINOR IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLAKES, MARKS, DISCLOSURES, GATE VESTIGE, AND SOFT FLASH THAT DO NOT AFFECT THE FIT, FORM OR FUNCTION OF THE PART ARE PERMISSIBLE PER DPNP-4.7-C5-01
4. REFERENCE MATING COMPONENTS OR EQUIVALENT:
SEE 15324795 (H590033) & 13755838 (H59012) ASSEMBLY DRAWINGS
33299380 ELBOW 90° WIRE DRESS
5. (1.5)X(1) DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY
6. APEX 2.8 4-WAY(4W) MALE AND FEMALE WIRE DRESSCOVER
7. INTERCHANGEABLE TOOL FOR 6MM, 9MM AND NO CONDUIT (CDT) OPTIONS
8. EJECTOR PIN NOTES:
ENGAGEMENT SURFACE FLUSH TO 0.15 MAX RECESSED OUTSIDE SURFACE FLUSH TO 0.05 MAX RECESSED
ALL OTHERS 0.10 MAX RAISED TO 0.25 RECESSED
9. ACCEPTANCE CRITERIA DEVIATIONS:
50N MIN FOR: BACKSHELL RETENTION AT WIRE EXIT BACKSHELL TO CONNECTOR RETENTION UNDER SIDE LOAD CONDUIT TO BACKSHELL RETENTION
35N MIN FOR: BACKSHELL RETENTION AT WIRE EXIT POST MOISTURE CONDITIONING
90N MIN FOR: BACKSHELL RETENTION AT WIRE EXIT POST ULTRAVIOLET EXPOSURE

[illegible]

LINE DRAWN THROUGH A PART NUMBER
INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE
FOR ORDERING.

PART NUMBER THAT DO NOT HAVE A LINE PERCENT INDICATE
THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING.

CONTACT DELPHI SALES TO ASSURE AVAILABILITY
OF PART.

990 TYPE

PART DRAWING

STYLE

VOLUME (10M)

SEE CHART

DISTR CODE

D

UNLESS OTHERWISE SPECIFIED

THIS DOCUMENT IS IN ACCORDANCE WITH MIL-STD-1916-1994
REQUIREMENT OF 100% DIMENSIONAL VERIFICATION AND
TOLERANCING (ANSI-ASME-2010). SEPARATE PATTERNS OF
DIMENSIONS SHALL BE OBTAINED SEPARATELY. REPEATABLITY OF
DIMENSIONS.

ALL DIMENSIONS ARE IN MILLIMETERS

THIRD ANGLE
PROJECTION

DO NOT
SCALE

USE MATH
DATA







DELPHI DELPHI PACKAGED ELECTRICAL/ELECTRONIC ARCHITECTURE Channel, India COPYRIGHT ©2015 DELPHI CORPORATION AND/OR ITS AFFILIATES, ALL RIGHTS RESERVED. REVISED: 2015 THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION AND CONTAINS DELPHI CONFIDENTIAL INFORMATION. NO REPRODUCTION OR TRANSMISSION OF ANY KIND OF THIS DOCUMENT OR ITS RELATED DOCUMENTS, IN ANY FORM, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.							
						DATE	
DR							
APV01	SAKTHIVEL M					26.0C15	
APV02	SAKTHIVEL M					26.0C15	
APV03	SUCHA SIAN					26.0C15	
APV04							
APV05		SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 1049901					
MATERIAL POLYAMIDE COMPOUND BLACK							
DRAWING NAME TAXI COV WIRE DRESS							
DRAWING NUMBER 33299375							
SIZE	SCALE	FRAME NO	SHEET NO	1ST	REV	N/P	
A4	2:1	1 OF 1	1 OF 1	R	11		